



| | | |
|--|---|---|
| General Features | Model No. | C32227T2 |
| | Panel (60Hz/120Hz/3D) | CSOT315A04-8 AN04 (60Hz) |
| | Destination Country | UK&EU |
| | Safety and Regulation | CE, ROHS |
| | Panel System | 31.5 inch LED Panel (Approx. 74cm) |
| | Purpose | TV/Monitor Optional |
| | Aspect Ratio | 16:9 |
| | Max. Resolution | 1366 x 768 |
| | Contrast Ratio (Typical) | 3000:1 (TYP) by panel |
| | Brightness (TYP cd/m2) | 250 nits (TYP) by panel |
| | Display Area (mm) | 697.68 (H) x 392.256 (V) |
| | Pixel Pitch (mm) | 0.51075 (H) x 0.51075 (V) |
| | Display Colors | 16.7M |
| | Viewing Angle (L/R/U/D) | 89/89/89/89 (CR ≥ 10) |
| | HD Supported Definitions | 1080p/1080i/720P/576P/480P |
| | Response Time (Tr+Tf/typ.) | 8ms |
| | AC Switch | N/A |
| | Cabinet Color | Piano/brush black |
| | Tilt Angle (up and down movement) | N/A |
| | Swivel Angle (left and right movement) | N/A |
| Wall Mounting Support(Screw Size) | VESA, 100 x 100mm (M4 x 7) | |
| Reception | TV Solution | S2TEK512 |
| | TV System | ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVB-T2, MPEG 2,MP@ML, MPEG 4 |
| | TV Band | ATV 49MHz - 863MHz DTV VHF (174MHz - 230MHz) UHF (474MHz - 862MHz) |
| | 5V from Antenna | N/A |
| | NTSC Playback | N/A |
| | Digital Comb Filter | 3D |
| | De-interlace Image Enhancement | N/A |
| | Tuning System | FST |
| | Clock / Time Display | N/A |
| | CI PLUS | N/A |
| | Number of channel for storing | 100 Analog / 400 Digital |

| | | |
|------------------------|--|---|
| Sound | Bass | YES |
| | Treble | YES |
| | Balance | YES |
| | Sound Mode | Standard / Music / Movie / Sports / User |
| | Stereo System | NICAM/A2 |
| | Audio Output | 2*6W |
| | Dolby | N/A |
| | SRS | N/A |
| Connectors Jack | RF Antenna | 1 |
| | HDMI | YES x 3 |
| | CVBS | YES x 1 |
| | PC In | D-sub 15Pin x 1 |
| | Audio In | PC audio x 1 (3.5 φ Mini Jack) CVBS Audio x1 |
| | Scart | YES x 1 |
| | YPbPr | YES x 1 |
| | Coax | YES x 1 |
| | Earphone Out | YES x 1 (3.5 φ Mini Jack) |
| | USB | YES x 1 (Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov,*.mkv,*.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png) |
| | CI | YES x 1 |
| | RCA | N/A |
| Other Features | APS | ATV, DVBT, DVBC storage in capture order |
| | OSD Language | English / French / German / Italian / Spanish / Portuguese |
| | Teletext | 1000 pages |
| | EPG (Electronic Program Guide) | 7 days (not 7 days from satellite transmissions) |
| | Automatic Tuning | YES |
| | Sleep Timer | YES (240min) |
| | Noise Reduction | YES |
| | Color Temperature Adjustment | YES |
| | Picture Mode | Standard / Dynamkic / Mild / User |
| | Home Mode | YES |
| | Sleep Mode | YES |
| | Hotel Mode | YES |
| Power | Power Supply | AC 100V-240V~ 50Hz/60Hz |
| | Operation Power Consumption | 35W |
| | Max power Consumption | <60W |
| | Standby Power Consumption | 0.4W |
| | Energy Efficiency Class | A |
| Accessories | USER'S Manual | ENGLISH |
| | Remote Control | YES x 1 |
| | Power Cable | YES x 1 |
| | Adapter | N/A |
| | Adapter Cables | N/A |
| | Warranty | YES |
| | Battery | 1.5V (AAA) x 2 |
| Dimensions | Unit Dimension With Stand (W x H x D mm) | 739 x 493 x 206 |
| | Unit Dimension Without Stand (W x H x D mm) | 739 x 441 x 92 |
| | Weight of unit (kg) | 6 |