

LUNAR Pro Deluxe Full 960H by **blupont**



8 Channel 4 Camera Kit with 1000GB Pre-Installed and Formatted

Full 960H Recording and Playback with Audio

GUI Designed in House and Offers Excellent and Simple Usability

Easy to Use App - Remote View from Anywhere in the World

Robust Metal Outdoor Cameras offer Crystal Clear Imaging

Box Contents:

1x	LUNAR Pro Deluxe Full 960H 8 Channel DVR by blupont
1x	1000GB Installed and Formatted
4x	blupont ™ 960H 1000 TVL IP66 Grey Camera - 24 LED
4x	18m CCTV Shotgun Cable (Video/Power)
2x	UK Power Adapter
1x	9-Way Power Splitter
1x	IR Remote Control
1x	USB Mouse
1x	Free Lifetime Technical Support

LUNAR DVR.
H.264 Full 960H DVR **4 Channel by blupont™**



System	User Interface	Graphic User Interface (OSD)
	O/S	Embedded Linux
	Operation Mode	Preview, Recored, Playback, Backup and Network
	Password Security	Multi-Level User Management
A/V INPUT	Video Input	8 CH BNC
	Audio Input	8 CH RCA
A/V OUTPUT	HDMI Output	Supports
	VGA Output	Supports
	Display	1/4/9 Optional
	Video Standard	PAL/NTSC
	Loop	NO
	CVBS Main Output	1 Out, BNC; Resolution: PAL: 704*576, NTSC: 704*480
	Spot Output	NO
	Audio Output	1 CH, RCA
A/V ENCODING PARAMETERS	Video Compression	H.264
	Display Frame Rate	PAL: 200FPS (8 X 25 FPS); NTSC: 240FPS (8 X 30 FPS)
	Recording Frame Rate	PAL: 200FPS (8 X 25 FPS); NTSC: 240FPS (8 X 30 FPS)
	Video Encoding Resolution	PAL:WD1:960 X 576/WCIF:480 X 288/D1:704 X 576/CIF:352 X 288
		NTSC:WD1:960 X 480/WCIF:480 X 240/D1:704 X 480/CIF:352 X 240
	Video Frame Rate	PAL: 1-25 FPS; NTSC: 1-30 FPS
	Video Bit Rate	WCIF(CIF): 384-768kbps, WD1(D1): 768-1536kbps
	Stream Type	Video & Audio/Video
	Audio Compression	ADPCM
	Recording Mode	Always/Schedule/Alarm Recording/Motion Detection Recording
	Video Search	Time/Channel/Event
	Audio Bit Rate	8-32kbps
	Dual-Stream	Supports
	Mobile Phone Monitor	Supports Android Phone/iPhone/iPad
	Recording Resolution	8CH WD1 Recording & 8CH WD1 Realtime Playback;
		8CH WCIF Recording & 8CH WCIF Realtime Playback;
		8CH D1 Recording & 8CH D1 Realtime Playback;
	Playback Symultaneously	1-8CH Optional
HDD	Type	1 Piece SATA
	Maximum Capacity	4TB for Each SATA
EXTERNAL CONNECTORS	Voice Talk	NO
	Record Mode	Audio & Video Recording Simultaneously
	Network Protocol	Supports IE/PPPoE/DDNS/DHCP
	Domain Server Name	Support 88110, Reelink, 3322, DYNDNS, NO-IP, Changeip,
		Dnsexit Domain name server as default value
	Network	1 RJ4510M/100M
	Serial Port	1 RS-485 Serial Port
	E-SATA Connector	Supports
	USB Connector	2 USB
	Firmware Update	Support USB update/Network Update
	Alarm Input	8 CH In
	Alarm Output	1 CH Out
	Operation Temperature	(-10°C~+55°C)
	Operation Humidity	(10%-90%)



blupont™ 1000 TVL 3.6mm Grey Bullet IP66 - 20m IR



Model	SC-100-BG-BL
Image Sensor	1/3"CMOS with IR cut
Effective Pixels	PAL:976(H)*596(V)
Horizontal Resolution	1000TVL
OSD Menu	NO
DNR	NO
Digital Wide Dynamic Range Adjustable	NO
Privacy Zone	NO
Min. Illumination	0.01Lux/F1.2
Power Supply	DC12V(±10%) 200mA
Backlight Compensation	ON/OFF
White Balance	Auto/Manual
Electronic Shutter	1/50(1/60)~1/100,000(sec)
IR Leds	24PCS IR Leds.
IR Range	20M
Waterproof	IP66
Lens	3.6mm lens
Signal System	PAL
S/N Ratio	>48dB
Video Output	1.0Vp-p, 75Ω
Sync. System	Internal
Operating Temperature	-30°C to +70°C
Lens Mount	CS Mount
G.W./PC	500G
Camera Size	115mmx50mm
Packing Size/PC	94*65*58mm

blupont™