



Customer Model	H40M2600
Front-cover Colour	Black
Comfort Features	<ol style="list-style-type: none"> 1. Automatic: Automatic format adjustment, automatic channel search 2. TV: HbbTV, EPG, favourite lists, Teletext, HD + ready (can be retrofitted via CI Slot), Astra 19.2 channel sorting (LCN) HD, parental control, Channel Edit, Favorites List 3. Netflix, YouTube, Wuaki.TV, arte, Toon Googles, Game Center, AppStore, Plex, Kidoz, AOL On, VIAWAY, Media, Accuweather, YuppTV, Apps Store 4. Support Audio, Video, Picture play from the Multi-Media 5. Other: Dolby Audio, DBX, HDMI ARC, HDMI CEC, MHL (Mobile High Definition Link), 802.11AC, built-in speaker, integrated media player, Anyview Cast (Users can do things like view pictures/video from a smartphone on a big screen television), Anyview Stream (DMP). Multilingual OSD
Panel Performance	
Aspect Ratio	16:9
Diagonal Screen Size	102cm/40inch
Resolution	FHD 1920x1080
Curvature Rate	0
Display Colours	10bits
Vsync Frequency	60Hz

Contrast	4000(Typ.)
Brightness (nits)	200(Typ.)
Local Dimming	-
FRC	-
3D technology	-
2D to 3D	-
Refresh Rate SMR Hz	200
Special	-
Improving Engines	
Processor	Quad Core (A7*4)
Upscaling Ultra HD	-
MEMC	-
Decoder	HEVC (H.265),H.264,MPEG4, MPEG2,VC1,MVC
Input Lags	Great <50ms
Media Player	Yes (Video, Audio, Picture)
3D Digital Comb Filter	Yes
Specialities	-
Sound	
Output Power Consumption	2x7W
NICAM / A2 Stereo	NICAM Stereo
User Equalizer	Yes
Sound - Special	DBX
Convenience	
Teletext (pages)	899
Multi-Language OSD	19Languages
Hotel TV	Yes
PVR	Yes
Time Shift	Yes

PC channel sorting	Yes
Special	NO
Internet	
Wireless LAN adapter Support	Yes
WiFi technology	802.11b/g/n,2.4G
BT	No
Apps	Yes (Netflix, YouTube, Wuaki.TV, arte, Toon Googles, Game Center, AppStore, Plex, Kidoz, AOL On, VIAWAY, Media, Accuweather, YuppTV)
Web browser	Yes
HbbTV	Yes(V1.5)
Anyview Cast	Yes(Users can do things like view pictures,Video from a smartphone on a big screen television)
Anyview Stream	Yes(DMP,DMR)
Reception	
Digital Reception(DVB)	DVB-T2/T/C/S2/S(Freeview HD)
Common Interface (CI)	Yes(V1.3)
Astra LCN	Yes
Special	No
Connecting Interface	
HDMI1	HDMI 1.4,CEC,MHL2.0
HDMI2	HDMI1.4,CEC,ARC
HDMI3	-
USB (2.0)	1
USB(3.0)	-
S/PDIF Output	1
Audio (L/R) Input	1
Headphone Output	1

RF Tuner	2
Composite (AV) Input	1
Component YPb(Cb)/Pr(Cr) Input	1
SCART	0
VGA Input	-
PC Audio Input (3.5mm)	-
Subwoofer	-
Ethernet RJ45 port	1
Eco & Power supply	
Power Supply	220V-240V 50Hz
Energy Efficiency Class	A+
Standby Consumption	≤0.5w
Power off	0W
Power Consumption (Nameplate) (W)	70
Annual consumption (Nameplate) (kWh)	102.2
Power Consumption (Energy Rating Label) (W)	46
Annual consumption (Energy Rating Label) (kWh)	69
Luminance Ratio(%)	>65%
Mercury content(mg)	0
Lead content	Yes-This television contains lead only in certain parts or components , in accordance with existing exemption clauses under the RoHS Directive.
Weight & Dimensions	
Net Weight/Gross Weight (Kg)	6.4/8.8
Package (Horizontal/Vertical)	Vertical
Out Package Size (LxDxH) (mm)	1005X140X635

Net Size With Base and Speakers (LxDxH) (mm)	916X206X573
Net Size Without Base and With Speakers (LxDxH) (mm)	916X81X542
EAN	6942147430170
Accessories	
Stand	Yes
between the two Stand distance	61.8cm
VESA Wall Mount Compatible (mm)	200x200
Remote control	Yes
Batteries	AAAx2
User Manual	Yes
Quick start page	Yes
Wires	No
Adaptor	No
Others	No
Logistics & Warranty	
Container Loading(40HQ)	768
DMP formats	
Container Format	AVI,MP4,MKV,TS,,FLV OGG,
Video	.AVI,.WMV,.MP4,.MOV,.3GP,.MKV,.MPG,.MPEG,.VOB,.RM,.FLV,. WebM,.VRO,.OGM,
Audio	.wma,.wmv,.mp4,.FLAC,.MP2,.MP3 (.mpg,.mpeg,. vro ,.vob,.flv,.mkv) music(mp3 aac wma flac mp2 wav)
Picture	.jpg,.bmp,.PNG,.GIF,. webp,.mpo,.jps,.pns