

	Product Photo	
General Feature	Customer Model No.(Brand)	C32ANSMT
	Model No.	
	Panel(60Hz/120Hz/3D)	ST315A04-8(60Hz)
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	31.5 inch LED Panel(Approx. 74cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1366 x 768
	Contrast Ratio (Typical)	3000:1(TYP) by panel
	Brightness(TYP cd/m2)	250nits(TYP) by panel
	Display Area(mm)	697.68 (H) x 392.256 (V)
	Pixel Pitch (mm)	0.51075 (H) x 0.51075 (V)
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	8ms
	AC Switch	N/A
	Cabinet Color	brush black
	Tilt Angle (up and down movement)	N/A
Swivel Angle (left and right movement)	N/A	
Wall Mounting Support(Screw Size)	VESA, 100 x 100mm(M5* 10)	
Reception	TV Solution	Mstar 3463
	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4 ,H.264
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
	Number of channel for storing	100 Analog / 400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*6W
	Dolby	N/A
	SRS	N/A
Connectors Jack	RF Antenna	1
	HDMI	YES*2(ver1.4a)

	CVBS	YES×1
	PC In	D-sub 15Pin × 1
	Audio In	Dual
	Scart	N/A
	YPbPr	YES× 1
	Digital Audio out	YES× 1
	Earphone Out	YESx 1(3.5 φ Mini Jack)
	USB on TV	YESx 1(Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	YES× 1
	RCA	N/A
	RJ45 on Android	YES× 1
	Mirco SD card on Android	YES× 1
	USB on Android	YESx 2(Multi Media & Wireless Mouse and Keyboard)
Other Features	APS	ATV, DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian/Spanish/Portuguese
	Teletext	1000pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamkic/Mild /User
	Wifi on Android	YES
	Home Mode	YES
	Hotel Mode	YES
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	34W
	Max power Consumption	<60W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A
Accessories	USER'S Manual	ENGLISH
	Remote Control	YES× 1
	Power Cable	YES× 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	738 x190 x 498mm
	Unit Dimension Without Stand (W x H x D mm)	738 x 76 x 446mm
	Weight of unit(kg)	6