

PS2 KVM Console Extender Cat5 Extender - 500 ft

StarTech ID: SV565UTPGB



The SV565UTPGB PS2 KVM Console Extender Cat5 Extender (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away.

Use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

For added convenience, the Console extender is compatible with any brand of PS/2 KVM Switch.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Use one or more servers in a server room from a remote location
- Monitor computer-controlled equipment in a factory or warehouse

Features

- Can be used with a single computer or connected to an existing KVM switch
- Supports auto-switching between host and remote users or dedicated control
- PS/2-based computers are supported at the host and remote locations
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
Multi-Monitor	No
PC Interface	PS/2
PC Video Type	VGA
Rack-Mountable	No
IP Control	No
Max Transfer Distance	150 m (492 ft)
Supported Resolutions	1280 x 1024 @ 300ft/ 100m 1024 x 768 @ maximum cable length
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Other Interface(s)	1 - RJ-45 Female
OS Compatibility	OS independent; No software or drivers required
Note	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
Center Tip Polarity	Positive
Input Current	0.2 A
Input Voltage	100 ~ 240 AC
Output Current	0.6 A
Output Voltage	9 DC
Plug Type	M
Power Source	AC Adapter Included
Humidity	0~80% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Color	Black
Product Height	2 cm [0.8 in]
Product Length	7.5 cm [3 in]
Product Weight	299 g [10.6 oz]
Product Width	15.5 cm [6.1 in]
Shipping (Package)	1.6 kg [3.5 lb]

Weight

Included in Package	1 - Local Unit
Included in Package	1 - Remote Unit
Included in Package	2 - Packs, Rubber Feet
Included in Package	2 - Power Adapters
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

