

Printview: Ferrule; sleeve for 4 mm<sup>2</sup> / awg 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-207

**WAGO**® online catalog / eShop

**Ferrule; sleeve for 4 mm<sup>2</sup> / awg 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90**

Item No.: 216-207



Ferrule; sleeve for 4 mm<sup>2</sup> / awg 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90

## Marking

RoHS ✓  
Compliant

## Business data

Supplier	WAGO
Item no.	216-207
GTIN / EAN	4017332277525
Content	1
Order amount	100
Customer item number	

## Notes

## Technical data

### Miscellaneous

Color	gray
Strip length 1	12 mm / 0.47 in
Fire load [MJ]	0.003 [MJ]
Weight [g]	0.27 [g]
Diameter [mm]	5.4 [mm]
Diameter 1 [mm]	4.8 [mm]
Diameter 2 [mm]	2.9 [mm]
Length [mm]	16.8 [mm]

Printview: Ferrule; sleeve for 4 mm<sup>2</sup> / awg 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-207

---

**Technical data**


<i>Length 1 [mm]</i>	<i>9.5 [mm]</i>
----------------------	-----------------

Printview: Ferrule; sleeve for 4 mm<sup>2</sup> / awg 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-207

---

**Images & drawings**





#### Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.