

Power tap; for 50 mm² high-current terminal blocks; module width 16 mm

Item No.: 285-447



Power tap; for 50 mm² high-current terminal blocks; module width 16 mm

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	285-447
GTIN / EAN	4045454549657
Content	1
Order amount	5
Customer item number	

Notes



Technical data

Miscellaneous

Total number of connection points	2
Total number of potentials	2
Color	gray
Ratings according to 1	IEC/EN 60947-7-1
Pollution degree (1)	3
Rated voltage EN (1) [V]	1000 [V]
Rated surge voltage (1) [kV]	8 [kV]
Nominal current [A]	41 [A]
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	0.2 ... 6 mm ² / 24 ... 10 AWG

Technical data	
<i>Fine-stranded wires 1</i>	<i>0.2 ... 6 mm² / 24 ... 10 AWG</i>
<i>Strip length 1</i>	<i>12 ... 13 mm / 0.47 ... 0.51 in</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Design</i>	<i>angled</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Fire load [MJ]</i>	<i>0.168 [MJ]</i>
<i>Weight [g]</i>	<i>13.001 [g]</i>
<i>Width</i>	<i>16 mm / 0.63 in</i>
<i>Module width [mm]</i>	<i>16 [mm]</i>
<i>Module width [inch] [inch]</i>	<i>0.63 [inch]</i>

Images & drawings



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.