

4-conductor end terminal block; with fixing flange; for screw or similar mounting types; fixing hole 3.2 mm Ø

Item No.: 264-331



4-conductor end terminal block; with fixing flange; for screw or similar mounting types; fixing hole 3.2 mm Ø

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	264-331
GTIN / EAN	4044918414579
Content	1
Order amount	100
Customer item number	

Notes

Technical data


Miscellaneous

Total number of connection points	4
Total number of potentials	1
Color	gray
Pollution degree (1)	3
Rated voltage EN (1) [V]	800 [V]
Rated surge voltage (1) [kV]	8 [kV]
Nominal current [A]	24 [A]
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	0.08 ... 2.5 mm ² / 28 ... 12 AWG

Printview: 4-conductor end terminal block; with fixing flange; for screw or similar mounting types; fixing hole 3.2 mm Ø - Item No.: 264-331

Technical data	
<i>Fine-stranded wires 1</i>	0.08 ... 2.5 mm ² / 28 ... 12 AWG
<i>Strip length 1</i>	8 ... 9 mm / 0.31 ... 0.35 in
<i>Note (conductor cross-section)</i>	12 AWG: THHN, THWN
<i>Type of wiring</i>	Front-entry wiring
<i>Design</i>	horizontal
<i>Marking level</i>	Center marking
<i>Fire load [MJ]</i>	0.112 [MJ]
<i>Weight [g]</i>	6.369 [g]
<i>Width</i>	10 mm / 0.394 in
<i>Height from the surface</i>	22.1 mm / 0.87 in
<i>Length</i>	32 mm / 1.26 in

Images & drawings



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.