

Printview: 1-conductor PCB terminal strip; 1 solder pin/pole, staggered; 2-pole; pin spacing 3.5 mm / 0.138 in; with push-button; with test port for 1.3 mm Ø test pin - Item No.: 250-202

WAGO® online catalog / eShop

1-conductor PCB terminal strip; 1 solder pin/pole, staggered; 2-pole; pin spacing 3.5 mm / 0.138 in; with push-button; with test port for 1.3 mm Ø test pin

Item No.: 250-202



1-conductor PCB terminal strip; 1 solder pin/pole, staggered; 2-pole; pin spacing 3.5 mm / 0.138 in; with push-button; with test port for 1.3 mm Ø test pin

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	250-202
GTIN / EAN	4044918648158
Content	1
Order amount	140
Customer item number	

Notes

Kompakte Klemmenleisten mit Betätigungsdrückern
Eindrähtige Leiter und feindrähtige Leiter mit Aderendhülsen
direkt steckbar
Drückerbetätigung für das Anschließen von feindrähtigen Leitern und das Lösen von Leitern
45°-Leitereinführung für komfortable und platzsparende Verdrahtung
Individuelle Farbkombinationen
Klemmenleisten auf Anfrage auch mit Rasterzwischenstücken erhältlich

Technical data

Miscellaneous


No. of poles	2
Total number of connection points	2
Total number of potentials	2
Color	gray
Ratings according to 1	IEC/EN 60664-1

Printview: 1-conductor PCB terminal strip; 1 solder pin/pole, staggered; 2-pole; pin spacing 3.5 mm / 0.138 in; with push-button; with test port for 1.3 mm Ø test pin - Item No.: 250-202

Technical data	
<i>Pollution degree (1)</i>	2
<i>Rated voltage EN (1) [V]</i>	320 [V]
<i>Rated surge voltage (1) [kV]</i>	4 [kV]
<i>Nominal current [A]</i>	8 [A]
<i>Degree of pollution (2)</i>	2
<i>Rated voltage EN (2) [V]</i>	630 [V]
<i>Rated surge voltage (2) [kV]</i>	4 [kV]
<i>Nominal current (2) [A]</i>	8 [A]
<i>Degree of pollution (3)</i>	3
<i>Rated voltage EN (3) [V]</i>	250 [V]
<i>Rated surge voltage (3) [kV]</i>	4 [kV]
<i>Nominal current (3) [A]</i>	8 [A]
<i>Connection technology (1)</i>	Push-in CAGE CLAMP®
<i>Conductor entry angle to the PCB 1 [°]</i>	45 [°]
<i>Type of wiring</i>	Front-entry wiring
<i>Solder pin arrangement</i>	staggered solder pin
<i>Solder pin length [mm]</i>	3.6 [mm]
<i>Solder pin width A [mm]</i>	0.4 [mm]
<i>Solder pin width B [mm]</i>	0.75 [mm]
<i>Fire load [MJ]</i>	0.026 [MJ]
<i>Weight [g]</i>	1.103 [g]

Printview: 1-conductor PCB terminal strip; 1 solder pin/pole, staggered; 2-pole; pin spacing 3.5 mm / 0.138 in; with push-button; with test port for 1.3 mm Ø test pin - Item No.: 250-202

Images & drawings



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.