


Samsung Printer *Xpress* M2835DW

Samsung Multifunction *Xpress* M2885FW

MONO LASER PRINTERS FOR TODAY'S MOBILE WORK ENVIRONMENT



YOU'VE GONE MOBILE, AND SO HAS YOUR PRINTER.

Today, small business means mobile business. That's precisely why we designed the Samsung Xpress M2835DW and M2885FW mono laser printers. Equipped with Samsung SMART Printing Solutions™, they link seamlessly with mobile devices enabling you to be more productive wherever work takes you. The NFC technology makes printing wirelessly from a mobile device a breeze. Just tapping your smartphone is all it takes. Adding to the innovation is sharp, professional document quality, the capability to print varying media types and eco-friendly printing options that help you save money. Everything, in other words, to help you meet the demands of today's modern business world.

CONTACT US:

1-800-SAMSUNG

samsung.com/printer

FOLLOW US:



[youtube.com/samsungprinting](https://www.youtube.com/samsungprinting)



[@Samsungtweets](https://twitter.com/Samsungtweets)

KEY FEATURES



Get Print on Tap

Near Field Communication (NFC) printing is a wireless sharing technology that enables your mobile device to connect and communicate with your printer. Simply tap your phone or tablet to your multifunction printer, and print.



Direct Printing Without an App

You can even print photos and web pages from GALAXY S® series devices without needing an app.¹



Be More Productive with 4-in-1 Versatility

The Samsung M2885FW is an all-in-one (AIO) device that lets you print, copy, scan and fax complex documents more quickly, easily and efficiently.



Professional Image Quality

Samsung's ReCP technology improves readability of printed documents by enhancing thin lines and sharpening the edges of negative text. You get sharp, solid prints with an effective print resolution output of up to 4800 x 600 dpi.



Print Diverse Media

Samsung Xpress printers are built to handle a wide range of media types. You can produce flyers and other collateral, on cardstock and other media, as heavy as 59 lb. bond.



Enjoy a Low TCO

Samsung high-yield toner cartridges help you reduce total cost of ownership. Samsung Eco Solutions let you save even more by lowering toner and paper usage, and reducing energy consumption.

¹There is also no app needed for iOS®-supported devices using AirPrint.™

SAMSUNG

Samsung Printer Xpress M2835DW

Samsung Multifunction Xpress M2885FW



KEY SPECIFICATIONS For complete product specifications, visit samsung.com/printer

Product	Model Number	M2835DW	M2885FW
	Function	Print	4-in-1 Print, Copy, Scan, Fax
	Value Added Features	Built-in Wireless, WPS (Wi-Fi Protected Setup), One-Touch Eco-Button, NFC	Built-in Wireless, WPS (Wi-Fi Protected Setup), One-Touch Eco-Button, NFC
Print	Speed	Up to 29 ppm	Up to 29 ppm
	Emulation	SPL (Samsung Print Language)/ PCL5e / PCL6	SPL (Samsung Print Language)/ PCL5e / PCL6
	Resolution	Up to 4,800 x 600 dpi	Up to 4,800 x 600 dpi
	First Page Out Time	Less than 8.5 Seconds	Less than 8.5 Seconds
	Duplex Print	Built-in	Built-in
Copy	Copy Speed	N/A	Up to 29 cpm
	Resolution	N/A	Up to 1200 x 1200 dpi
	First Copy Out Time	N/A	Less than 14 Seconds
	Zoom Range	N/A	25% to 400%
	Multi Copy	N/A	1-99 Pages
	Copy Features	N/A	ID Copy, N-Up, Reduce/Enlarge, Book Copy
Scan	Scan Compatibility	N/A	TWAIN, WIA
	Scan Method	N/A	Color CIS
	Resolution (Optical/Enhanced)	N/A	1200 x 1200 dpi/Up to 4800 x 4800 dpi
	Scan Depth (Mono/Color)	N/A	8 bit / 24 bit
	Scan Speed	N/A	Up to 17 ipm
	Scan To	N/A	PC, Network
Fax	Compatibility	N/A	ITU-T G3, ECM
	Communication System	N/A	PSTN / PABX
	Modem Speed	N/A	33.6 Kbps
	Fax Memory (Max.)	N/A	600 pages (8 MB)
	Fax Features	N/A	Color, On Hook Dial, Search, Speed Dial, TAD I/F, Pause, Auto Redial, Last Number, Distinctive Ring, Caller ID, External Phone Interface, Tx / Rx Journal, Confirmation, Fax to PC, Delayed Fax
Paper Handling	Input Capacity	250 sheets	250 Sheets
	Output Capacity	150 sheets	120 Sheets
	Media Size	3" x 5" – 8.5" x 14"	3" x 5" – 8.5" x 14"
	Media Type	Plain, Thin, Thick, Thicker, Cardstock, Transparency, Pre-Printed, Recycled, Archive, Bond, Label, Envelope, Thick Envelope, Cotton, Colored	Plain, Thin, Thick, Cardstock, Hole Punched, Transparency, PrePrinted, LetterHead, Recycled, Archive, Bond, Label, Envelope, Cotton, Colored, Glossy, Thicker Paper
	Media Weight	16 – 59 lbs.	16 – 59 lbs.
	ADF Capacity	N/A	40 Sheets
	ADF Document Size	N/A	Width: 5.6" x 8.5"
General	Processor	600 MHz	600 MHz
	Memory (Max.)	128 MB	128 MB
	OS Compatibility	Windows (32/64 bit) XP/2003/Vista/2008/7/8/2008 R2/Server 2012, Mac OS X 10.5–10.9, Various Linux, Various UNIX	Windows (32/64-bit) 2000/XP/2003/2008 Server/Vista, Windows 7, Various Linux, OS Mac OS X 10.3 – 10.7
	Interface	Hi-Speed USB 2.0, Ethernet, 802.11b/g/n Wireless, Wi-Fi Direct	Hi-Speed USB 2.0, 802.11b/g/n Wireless, Wi-Fi Direct
	Mobile Printing	Samsung Mobile Print App, Google Cloud Print, AirPrint	Samsung Mobile Print App, Google Cloud Print, AirPrint
	User Interface	N/A	2-line LCD
	Noise Level	Less than 50 dBA Printing	Less than 50 dBA Printing
	Power Consumption	400 W (Printing), 45 W (Standby), 1.3 W (Sleep), 1.8 W (Sleep with Wi-Fi Direct), 1.2 kWh TEC, 1.3 kWh TEC (with Wi-Fi Direct)	400 W (Printing), 45 W (Standby), 1.6 W (Sleep), 2.4 W (Sleep with Wi-Fi Direct), 1.25 kWh TEC, 1.4 kWh TEC (with Wi-Fi Direct)
	Monthly Duty Cycle	12,000 images per month	12,000 images per month
	Unit Dimensions (W x D x H)	14.5" x 13.2" x 8.0"	15.8" x 14.3" x 14.4"
	Box Dimensions (W x D x H)	17.8" x 16.5" x 13.0"	18.3" x 16.8" x 19.5"
	Unit Weight	16.4 lbs.	24.9 lbs.
	Box Weight	21.2 lbs.	31.1 lbs.
	Consumables	Starter Toner Yield	1,200 pages
Toner		Black Standard: 1,200 page toner yield (MLT-D116S) Black High: 3,000 page toner yield (MLT-D116L)	Black Standard: 1,200 page toner yield (MLT-D116S) Black High: 3,000 page toner yield (MLT-D116L)
Toner Metrics		Declared Yields in Accordance with ISO/IEC 19752	Declared Yields in Accordance with ISO/IEC 19752
Imaging Unit		Black Imaging Unit: 9,000 pages (MLT-R116)	Black Imaging Unit: 9,000 pages (MLT-R116)
Accessories	Included	Set / Toner Cartridge / Imaging Unit / Power Cable / Manual User's Guide* / Driver CD (Driver / EUG / Application) / Quick Installation Guide / Warranty Card* / Product Registration Card* / Service Card* / USB Cable* / Tel Line Cord. Item(s) with* mark may not be supplied by some countries.	Set / Toner Cartridge / Power Cable / Manual User's Guide* / Driver CD (Driver / EUG / Application) / Quick Installation Guide / Warranty Card* / Product Registration Card* / Service Card* / USB Cable* / USB Cable* Item(s) with* mark may not be supplied by some countries.

CONSUMABLES For a complete list of accessories, visit samsung.com/printer

MLT-D116S
Black Standard Toner Cartridge,
1,200-page yield



MLT-D116L
Black High-Yield Toner Cartridge,
3,000-page yield



MLT-R116
Average Drum Yield
9,000-pages



SAMSUNG Toner Recycling Program
samsung.com/starus



For complete product information and accessories, visit samsung.com or samsung.com/printer

Product Support: 1-800-SAMSUNG | Follow us: [youtube.com/samsungprinting](https://www.youtube.com/samsungprinting) | @Samsungtweets