

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0357450410](#)  
**Status:** **Active**  
**Overview:** [VersaBlade™ Wire-to-Wire Connector System](#)  
**Description:** [VersaBlade™ .070 Male Crimp Terminal, 24 AWG, Type A](#)

**Documents:**

[3D Model](#) [Product Specification PS-35180-003 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family [Crimp Terminals](#)  
Series [35745](#)  
Application [Power](#)  
Crimp Quality Equipment [Yes](#)  
Overview [VersaBlade™ Wire-to-Wire Connector System](#)  
Product Name [VersaBlade™](#)  
UPC [756054339091](#)

**Physical**

Gender [Male](#)  
Material - Metal [Brass](#)  
Material - Plating Mating [Tin](#)  
Material - Plating Termination [Tin](#)  
Net Weight [0.253/g](#)  
Packaging Type [Reel](#)  
Plating min - Mating [0.813µm](#)  
Plating min - Termination [0.813µm](#)  
Termination Interface: Style [Crimp or Compression](#)  
Wire Insulation Diameter [2.20mm max.](#)  
Wire Size AWG [24, 26](#)  
Wire Size mm² [N/A](#)


**Solder Process Data**

Lead-freeProcess Capability [N/A](#)

**Material Info**

**Reference - Drawing Numbers**

Product Specification [PS-35180-003](#)  
Sales Drawing [SD-35745-001](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

**Search Parts in this Series**

[35745](#) Series

**Mates With**

[35746](#) Crimp Terminal

**Use With**

[35150](#) VersaBlade™ Hybrid Receptacle  
Housing. [35151](#) VersaBlade™ Hybrid Plug  
Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool

[0638132700](#)

Hand Crimp Tool for 0638196800  
Industry standard  
1.78mm Terminals  
Hand Crimp Tool for 0638196900  
Industry standard  
1.78mm Tab  
Terminals, 24-26  
AWG Wire  
FineAdjust™ 0639020700  
Applicator for .070  
Female Crimp  
Terminal.  
T2 Terminator 0639120700  
for .070 Female  
Crimp Terminal

This document was generated on 07/12/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**