

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0357460410](#)
Status: **Active**
Overview: [VersaBlade™ Wire-to-Wire Connector System](#)
Description: [VersaBlade™ .070 Female Crimp Terminal, 24 AWG, Type A](#)

Documents:

[3D Model](#) [Product Specification PS-35180-003 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [35746](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [VersaBlade™ Wire-to-Wire Connector System](#)
Product Name [VersaBlade™](#)
UPC [756054339107](#)

Physical

Gender [Female](#)
Material - Metal [Phosphor Bronze](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.253/g](#)
Packaging Type [Reel](#)
Plating min - Mating [0.813µm](#)
Plating min - Termination [0.813µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [2.20mm max.](#)
Wire Size AWG [24, 26](#)
Wire Size mm² [N/A](#)


Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Reference - Drawing Numbers

Product Specification [PS-35180-003](#)
Sales Drawing [SD-35746-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[35746](#) Series

Mates With

[35745](#) Crimp Terminal

Use With

[35150](#) VersaBlade™ Hybrid Receptacle Housing. [35151](#) VersaBlade™ Hybrid Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Extraction Tool

Product #

[0638132700](#)

Hand Crimp Tool for 0638196800
Industry standard
1.78mm Terminals
Hand Crimp Tool for 0638196900
Industry standard
1.78mm Tab
Terminals, 24-26
AWG Wire
FineAdjust™ 0639014300
Applicator for .070
Female Crimp
Terminal.
T2 Terminator 0639114300
for .070 Female
Crimp Terminal

This document was generated on 07/11/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION