

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0082283020](#)
Status: **Active**
Description: 1.00mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded, Tinned, 20 Circuits, Reel 30.48m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR61126
 UL E61522

General

Product Family Cable
 Series [24500](#)
 Crimp Quality Equipment Yes
 Geographic Area Asia
 Product Name Ribbon
 UPC 800754378895

Physical

Cable Length 30.48m
 Circuits (Loaded) 20
 Insulation PVC
 Net Weight 1156.720/g
 Packaging Type Reel
 Pitch - Termination Interface 1.00mm
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 28
 Wire/Cable Type (7x36) Stranded, Tinned

Electrical


Current - Maximum per Contact N/A
 Voltage - Maximum 300V

Material Info

Old Part Number 24500-20-100B

Reference - Drawing Numbers

Sales Drawing SD-24500-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[24500](#) Series

Use With

70121 MX-50™ Slimline Ribbon Cable.
 90584 Picoflex® PF-50 IDT Receptacle