

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000075](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 18-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0076 (Loose)
Product Name	Mini-Fit®
UPC	800754394093

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.126/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Old Part Number	5558GS4
-----------------	---------

Reference - Drawing Numbers

Sales Drawing	SD-5558-002
---------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description

FineAdjust™
Applicator for
Insulation OD

Product #

[0639002900](#)

1.65-2.05mm, 18-24
 AWG Wire
 Hand Crimp Tool for [0638190900](#)
 Male and Female
 Crimp Terminals,
 16-24 AWG Wire
 Extraction Tool [0011030044](#)
 FineAdjust™ [0639002600](#)
 Applicator for
 Insulation OD
 2.50-2.95mm, 18-24
 AWG Wire
 FineAdjust™ [0639015600](#)
 Applicator for
 Insulation OD
 1.90-2.30mm - 18-24
 AWG
 FineAdjust™ [0639023900](#)
 Applicator for
 Insulation OD
 1.40-1.70mm - 18-24
 AWG
 FineAdjust™ [0639024900](#)
 Applicator for
 Insulation OD
 2.30-2.60mm - 18-24
 AWG
 T2 Terminator™ [0639102600](#)
 for insulation OD
 2.50-2.95mm - 18-24
 AWG
 T2 Terminator™ for [0639102900](#)
 insulation OD 1.65
 – 2.05mm – 18 – 24
 AWG
 T2 Terminator™ [0639124800](#)
 for insulation OD
 2.50-2.95mm
 optimized for 18
 AWG only
 T2 Terminator™ [0639124900](#)
 for insulation OD
 2.30-2.60mm - 18-24
 AWG
 FineAdjust™ [0639024800](#)
 Applicator for
 Insulation OD
 2.50-2.95mm
 Optimized for 18
 AWG Only
 T2 Terminator™ [0639115600](#)
 for insulation OD
 1.90-2.30mm - 18-24
 AWG
 T2 Terminator™ [0639123900](#)
 for insulation OD
 1.40-1.70mm - 18-24
 AWG

This document was generated on 07/12/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION