

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847020006](#)
Status: **Active**
Overview: [Brad® Industrial Ethernet Solutions](#)
Description: Receptacle, RJ-45, Punchdown Panel Mount Receptacle Jack

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	84702
IP Rating	IP67
MolexKits	Yes
Overview	Brad® Industrial Ethernet Solutions
Product Name	RJ45
Type	110 Punchdown
UPC	822348263059

Physical

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	N/A
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Orientation	Straight
Panel Mount	Front
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-84702-004
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[84702](#) Series

Mates With

[84700-0002](#) Plug, [84702](#) Cable Assemblies

Use With

[84700-0003](#) Dust Cover

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION