

**Weller**  
**25 Watts, 120v, 750°F Professional Soldering Iron, 3-wire Cord**



◀◀ previous print close next ▶▶

**Product Details**

<b>Catalog No.</b>	<b>WP25</b>
<b>UPC Code</b>	<b>037103593597</b>
<b>Type</b>	<b>Temperature Controlled</b>
<b>Wattage</b>	<b>25 W</b>
<b>Temperature Range</b>	<b>750° F</b>
<b>Cord Length</b>	<b>6 ft.</b>
<b>Components Supplied</b>	<b>ST3</b>
<b>Packaging</b>	<b>Peg Hook/Retail Packaging</b>
<b>Tech. Spec.</b>	<b><u>Solder Safety Warnings.pdf</u></b>
<b>Lineart</b>	<b><u>WP25.pdf</u></b>
<b>Low Res. Image</b>	<b><u>WP25_100.jpg</u></b>
<b>High Res. Image</b>	<b><u>WP25_300.jpg</u></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

**Package Details (Dimensions)**

Email this Page

**Product Features:**

- **Ideal for a wide variety of electronic tasks, has ST3 soldering tip**
- **Uses ST series long life double-coated iron-plated tips**
- **Tip temperature: 750°F**
- **Quick change knurled collar, stainless steel barrel**
- **Light blue with cushion grip handle and plug-in heating element**
- **6' 3-wire cord, iron is 7 7/8" long**
- **IMPORTANT: Use only Weller® tips**
- **UL and cUL listed (120 VAC units only)**