

## Xcelite 5" General-purpose Shearcutter with Static-dissapative Black Grips



◀◀ previous   print   close   next ▶▶

### Product Details

<b>Catalog No.</b>	<b>175D</b>
<b>UPC Code</b>	<b>037103030009</b>
<b>Description</b>	<b>Diagonal</b>
<b>Jaw Type</b>	<b>Flush</b>
<b>Jaw Length</b>	<b>3/4 in.</b>
<b>Head Width</b>	<b>11/32 in.</b>
<b>Head Thickness</b>	<b>1/2 in.</b>
<b>Tip Dimensions</b>	<b>5/64 in.</b>
<b>Packaging</b>	<b>Peg Hook/Retail Packaging</b>
<b>Tech. Spec.</b>	<b><u><a href="#">170M_Specifications.pdf</a></u></b>
<b>Low Res. Image</b>	<b><u><a href="#">170D_100.jpg</a></u></b>
<b>High Res. Image</b>	<b><u><a href="#">170D_300.jpg</a></u></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

### Package Details (Dimensions)

[Email this Page](#)

#### Product Features:

- **Low profile, general-purpose cutter**
- **Superior blade by-pass shear cutting action**
- **Better cuts with half the effort**
- **Greatly reduced mechanical shock delivered to the work**
- **Features static-dissapative black grips**
- **Especially hardened and plated**
- **Features safety clips**
- **Flush cuts soft wire up to 20 AWG (0.8mm)**