


SMD Common Mode Choke Coils for DC and Signal Lines

CM04RC10T



■ Features

- Item Summary
100 Ω, 4 A, 9.0x5.2x4.7mm
- Lifecycle Stage
Discontinued
- Standard packaging quantity (minimum)
Taping 1500pcs

■ Products characteristics table

No. of Lines	2
Common Mode Impedance (typ)	100 Ω at 200MHz
Case Size (mm)	9.0x5.2
DC Resistance (max)	20 mΩ
Rated Current (max)	4 A
Rated Voltage (max)	50 V
Operating Temp. Range	-25 to +105 °C (Including-self-generated heat)
Insulation Resistance (min)	100 MΩ
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension A	9.0 ± 0.5 mm
Dimension B	5.2 ± 0.2 mm
Dimension C	4.4 ± 0.3 mm