


SMD Power Inductors (NR series)

NR6012T4R0NE



■ Features

- Item Summary
4.0uH±30%, 1.57A, 6.0x6.0x1.2mm
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 1000pcs

■ Products characteristics table

Inductance	4.0 uH ± 30 %
Case Size (mm)	6.0x6.0
Rated Current (max)	1.57 A
Saturation Current (max)	1.8 A
Temperature Rise Current (max)	1.57 A
DC Resistance (typ)	0.105 Ω
DC Resistance (max)	0.126 Ω
LQ Measuring Frequency	100 kHz
Self Resonant Frequency (min)	39 MHz
Operating Temp. Range	-25 to +120 °C (Including-self-generated heat)
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	6.0 ±0.2 mm
Dimension W	6.0 ±0.2 mm
Dimension H	Max 1.2 mm
Dimension e	1.35 ±0.2 mm

■ Recommended Land Patterns

【推奨ランドパターン】
実装上の注意
・実装状態を確認の上ご使用くださいようお願いいたします。
・本製品のはんだ付けはリフローはんだ工法に限ります。

【Recommended Land Patterns】
Surface Mounting
・Mounting and soldering conditions should be checked beforehand.
・Applicable soldering process to these products is reflow soldering only.

