

Mondopad

The all-in-one touchscreen collaboration system for video conferencing, whiteboarding, data sharing, and more





Work Better Together

In-room and remote visual collaboration made easy



InFocus Mondopad elegantly blends video calling, whiteboarding and more into one giant touchscreen PC for efficient face-to-face collaboration with people in any location. Bridge communication gaps, strengthen teams, capture and share information, train more effectively, and save time and money. You'll never want to meet without it.

Key Features

- Big, bright touch display everyone in the room can see
- Choose incredibly sharp 4K or 1080p HD resolution
- Native HD video calling and data sharing that's crystal clear
- Interactive whiteboard and on-screen annotation
- BYOD-friendly to connect and share with any device
- Built on a fast and flexible i7-based Windows PC
- Wireless keyboard and mouse included



Bring Your Display to Life with 4K

Our 80-inch Mondopad now features 4K resolution for an incredibly sharp, vivid picture. Boost the impact of your content and make every meeting or presentation more engaging, informative, and memorable with 4K.

- More pixels mean more detail and depth for amazingly life-like images
- Enhanced color rendering
- Presenters benefit from crisp, clear images up close
- Audiences enjoy vibrant, detailed images, even from the back of a conference room



See faces and content side by side with dual-stream video conferencing capabilities. You can even split them onto a second touch display – one display shows participants' faces while the other shows content.

“The way InFocus enables our agency to clearly connect with one another face to face, from our six different locations throughout the world, helps us to be more cohesive and builds more trusting teammate relationships, resulting in better work.”

—Gabe Winslow, Partner, Sq1

Video Connect to the World

Instantly bring people together from anywhere in the world to visually collaborate on the same content and do better work in less time.

InFocus video calling service is included for the first year, so you can make and receive video calls right away – or add your own video conferencing client onto Mondopad as you would on any other PC.

Have instant 4-way conversations on a Mondopad when you upgrade to InFocus 121 Premium video calling service.

Bring up to 25 people together with InFocus' cloud-based ConX Video Meeting service. Users can connect from other Mondopads, ConX Walls, PCs, Macs, tablets or smartphones.

Interactive Whiteboard

Stop taking pictures of your stained, old-fashioned whiteboard and step up to the digital Mondopad. Brainstorm, capture, and share your ideas on an interactive whiteboard without borders or barriers.


- Capture, save, and email whiteboard notes directly from the Mondopad
- Create a whiteboard on a canvas up to 100 display screens in size
- Paste backgrounds and images onto a whiteboard and annotate on top
- Write or draw with a complete collection of digital pens, shapes, lines, and colors



View, Annotate, and Share

Never lose an idea. Quickly and easily take notes on anything you're presenting and then save the changes.

- Use the same whiteboard tools to mark-up whatever you're presenting
 - Documents, presentations, spreadsheets, images, etc.
 - Web pages
 - Videos
- Save your notes as an image and email it directly from the Mondopad.
- Manage common or secure files accessed by email, office network, USB drives, and cloud-based services like Dropbox



“With the unique ability of the Mondopad to draw and annotate, our personnel in their respective classrooms can see anything the instructor is talking about.”

—Mike Heimbecker, Fire Inspector, Addison Fire Protection District

Bring Your Own Device

Participants can securely connect and share content with Mondopad from PCs, Macs, tablets or smartphones – making meetings more collaborative, productive and sustainable.

- Cast your device's screen to the Mondopad
- View up to four AirPlay or Chrome casts simultaneously
- Control the Mondopad with your device from anywhere in the room—advance slides, browse the web, annotate
- See what's being presented on the Mondopad from your device
- People can also make video calls to your Mondopad from a PC, Mac, tablet or smartphone



Wide-angle HD camera and noise-cancelling microphone array accurately capture the sights and sounds of the room.

Speaker bars deliver clear voices and powerful multimedia to the whole room.

Accessories / Solutions

InFocus products work together so you can collaborate effectively in and out of the conference room.

Video and Audio Solutions

Provide and capture the best views and sounds in the room for efficient and clear communication.

RealCam PTZ Camera (INA-PTZ-3): True HD 1080p resolution and pan/tilt/zoom with included remote control

Thunder Speakerphone (INA-TH150): VoiceAware anti-echo & noise-reducing technology for any size meeting room



RealCam PTZ
Camera

Videoconferencing Solutions

Collaborate with multiple participants and share faces and data on-demand.

ConX Video Meeting: Secure cloud-based video meeting rooms for up to 25 participants on nearly any device (get a FREE trial at infocusconx.com)

121 Premium (IN121PRM-1Y, IN121PRM-2Y, IN121PRM-3Y): Add 4-way videoconferencing and custom SIP address capabilities to your Mondopad. Upgrade from 121 Basic to 121 Premium with IN121PRM-UPG. Have SIP addresses with your domain name with IN121PRM-DOM.

121 Basic (IN121-1Y, IN121-2Y, IN121-3Y): Standard 2-way video call dial tone and SIP address (free for first year of Mondopad ownership)

ConX Phone (MVP100): Easy-to-use desk video phone for on-demand video communication from remote locations



Thunder Speakerphone

Display Solutions

Enhance the usability of Mondopad with these touchscreen solutions.

JTouch (INF5701p, INF6502WBp, INF7001ap, INF7002WB, INF8002): Extend your Mondopad's desktop to a second touch display and show two apps at once

Q Tablet (INP-120Q32X, INP-120Q32X-PR): Follow or control your Mondopad from around the room with this full-featured 10.1-inch Windows 10 Pro tablet



ConX Phone

Mounting Solutions

Mount your Mondopad on the wall or on a cart and roll it wherever it's needed to maximize its versatility.

MODEL	INF5720	INF6521 / INF6521AG	INF7021	INF8022
Wall Mounts		INF-WALLMNT2, INF-WALLMNT3		INF-WALLMNT3
Mobile Carts		INF-MOBCART, INF-MOBCARTPRO-B		INF-MCART-PL
Deluxe Mobile Cart w/ PTZ Mount & Accessory Shelf		INA-MCARTDX		
Floor Stand		INF-FLRSTND		N/A
Accessory Trays		INF-ACCYSHELF, INF-ACCYSHELFPRO-B		
Lift Assist Mounts		INA-MNTBB70	INA-MNTBB95	N/A
		INA-CARTBB, INA-SUPPORTBB, INA-VESABB		N/A
Camera Shelves		INF-PTZMNTU, INFPTZMNTL (attach to display), INF-VIDSHELF2 (attach to INF-WALLMNT2, INF-WALLMNT3, INF-MOBCARTPRO-B or INF-MCART-PL)		
		INF-VIDSHELF (attach to INF-MOBCART or INF-FLRSTND)		N/A
ATA Lift Cases	CA-ATALIFT55	CA-ATALIFT70		N/A

Warranty, Maintenance and Training Services

Get the most out of your Mondopad and protect your investment with these valuable services.

MODEL	INF5720	INF6521 / INF6521AG	INF7021	INF8022
Extended Hardware Warranty Plans	EPWHW57MP1 EPWHW57MP2	EPWHW65MP1 EPWHW65MP2	EPWHW70MP1 EPWHW70MP2	EPWHW80MP1 EPWHW80MP2
Extended Premium (Warranty & Software) Plans	EPWPRE57MP1 EPWPRE57MP2	EPWPRE65MP1 EPWPRE65MP2	EPWPRE70MP1 EPWPRE70MP2	EPWPRE80MP1 EPWPRE80MP2
Software Maintenance Plans	EPWSOFTPLAN1, EPWSOFTPLAN2			
Training Services	INF-VT2, INF-VT4			

DISPLAY	INF5720	INF6521 / INF6521AG	INF7021	INF8022
Size	57"	65"	70"	80"
Resolution	Full HD (1920 x 1080)			4K (3840 x 2160)
Anti-Glare	No	Yes**	No	Yes & Gorilla Class
Refresh Rate	120 Hz			
Viewing Angle	176°	178°	176°	
Pixel Pitch	0.67 mm	0.248 (H) x 0.744 (V)	0.63 mm	0.49 mm
Response Time	9.5 ms	6.5 ms	6 ms	6.5 ms
Contrast Ratio	5000:1		4000:1	3000:1
Brightness	370 cd/m ²	350 cd/m ²		500 cd/m ²
Video Input Compatibility	Full NTSC, 480i, 480p, 720p, 1080i, 1080p			Full NTSC, 480i, 480p, 720p, 1080i, 1080p, 4K
Inputs	HDMI x 2, VGA (HD15 VESA), component, RS232, 3.5mm stereo audio in, RCA stereo audio in, 3.5mm microphone in, USB Type-A x5 (4 on front, 1 on top used by camera) USB Type-B to touch screen controller board	HDMI x 4, VGA (HD15 VESA), component, RS232, 3.5mm stereo audio in, RCA stereo audio in, 3.5mm microphone in, USB Type-A x5 (4 on front, 1 on top used by camera) USB Type-B (for touch control)	HDMI x 2, VGA (HD15 VESA), component, RS232, 3.5mm stereo audio in, RCA stereo audio in, 3.5mm microphone in, USB Type-A x5 (4 on front, 1 on top used by camera) USB Type-B to touch screen controller board	DisplayPort 1.2, HDMI 2.0 x2 (rear), HDMI 1.4 (rear), VGA, component, 3.5mm audio in, RCA stereo in, RS232 serial, USB Type-A x5 (4 on front, 1 on top used by camera), USB Type B (for touch control)
Outputs	RCA stereo audio out (for sound bars), 3.5mm stereo out			
Touch Screen	Edge-to-edge multi-touch system with support for 5 point gestures	Edge-to-edge 10-point projected capacitive touch	Edge-to-edge multi-touch system with support for 5 point gestures	
Speakers (Integrated)	Stereo 7W x 2	Stereo 10W x 2	Stereo 7W x 2	
Power	AC 100 to 240V, 50/60Hz			
Mount	VESA standard 400 x 400mm, M6 screws			N/A
PC	INF5720	INF6521 / INF6521AG	INF7021	INF8022
Processor	Intel® Core i7-4770T, Q87 chipset with Intel vPro™ technology; Intel HD Graphics 4600			Intel Core i7-6700T, Q170 chipset with Intel vPro™ technology; Intel HD Graphics 530
Memory	8 GB RAM			
Hard Drive	SSD 120GB	SSD 128 GB	SSD 120GB	SSD 256GB
LAN (2x)	802.3 10/100/1000 Base-T with Wake on LAN			
Wi-Fi	Dual band 802.11 a/b/g/n MIMO PCIe half mini card, 2.4 GHz with Intel, AMT support			
Input Connections	USB Type-A x 7 (4 on side of display, 1 on top of display (used by camera), 2 on PC), Ethernet (RJ45 x 2)			
Output Connections	HDMI out			DisplayPort 1.2 out
Bluetooth	4.0			
Operating System	Windows 7 Pro 64bit			Windows 10 64-Bit Professional
Included Software	Microsoft Office Home & Business 32bit, Mondopad interface software			
SYSTEM	INF5720	INF6521 / INF6521AG	INF7021	INF8022
Product Dimensions (with camera & sound-bars)	56.7 x 3.7 x 40.7 in / 1388 x 91 x 998 mm	59.8 x 3.2 x 41.1 in / 1520 x 81 x 1044 mm	65.7 x 4 x 45 in / 1669 x 102 x 1143 mm	74.8 x 4 x 46.3 in / 1900 x 101 x 1176 mm
Product Weight	139.5 lbs / 63.3 kg	123.5 lbs / 56 kg	170 lbs / 77.1 kg	175 lbs / 79.4 kg
Shipping Dimensions	63.5 x 10 x 42.5 in / 1613 x 254 x 1080 mm	69 x 10.6 x 44.4 in / 1752 x 270 x 1128 mm	73 x 10.5 x 49 in / 1854 x 267 x 1245 mm	83.5 x 10.5 x 53.5 in / 2121 x 267 x 1359 mm
Shipping Weight (monitor, PC & camera) & (soundbars)	154 lbs / 70 kg 17.4 lbs / 7.9 kg	154.5 lbs / 70.1 kg	173 lbs / 78.5 kg 17.4 lbs / 7.9 kg	202 lbs / 91.6 kg 17.4 lbs / 7.9 kg
Soundbars Shipping Dimensions	30.4 x 12.3 x 6.7 in / 772 x 313 x 169 mm			
Accessories Included***	Wireless keyboard (where allowed), wireless mouse (where allowed), stylus, VGA cable, USB cable, security screws, security screw removal tool, power cord, remote, quick setup guide, sound bar assembly, camera assembly, foot assembly (feet included with INF5720 only)			
Warranty	1 year limited, extended warranties available			
Operating Temperature	41 to 95°F at 0 to 10K ft / 5 to 35°C at 0 to 3,048 m			
Power Consumption	250W max	150W Max	275W max	350W max
Noise	<40dBA @ 77°F / 25°C			

* Product specifications, terms, and offerings are subject to change at any time without notice.

** Anti-glare available in select regions; subject to change.

*** Keyboard, mouse and/or speaker bar may not be shipped to all countries.

Video Conferencing

Video call types

SIP, H.323, Skype, Lync

Codecs

Audio: CN 16k, CN 8k, G.722, G.722.1 baseline (24 kbps), G.722.1 baseline (32 kbps), G.722.1C (24 kbps), G.722.1C (32 kbps), G.722.1C (48 kbps), PCMA (ALow), PCMU (ULow), H.224 (telephone-event), x-msrta 16k, x-msrta 8k, G.729AB
Video: H.263, H.263+, H.263+, H.264 AVC packetization 0 and 1, XVD, x-msrvt

Camera and Microphones

Resolution: 1280 x 720

Frame rate: 30 fps at HD with H.264+YUV (2-way)

Lens and Field of View: 70° horizontal, 56° vertical, F/2.0, 3P

Lens: FOV(D) 56.8" in HD mode, FOV(D) 50" in VGA mode 1.0x

zoom, FOV(D) 30" in VGA mode 1.6x zoom

Audio support: 3 built-in Unidirectional microphones

Interface: USB 3.0 High Speed

Focus: Auto focus

Tilt: Manual up/down and left/right ±40°

Soundbars


Power: 100 - 240 volts AC, 50 - 60Hz

Speaker Drivers (L&R Channel): Two 3" and one 3/4" Aluminum Neodymium Tweeter (per side)

Power Output (RMS): 25 watts/channel @ 1% THD, 1KHz,

2-channels drive, 70 watts total system PEAK

Frequency Response: 90 Hz to 20 KHz



InFocus

InFocus Corporate HQ

13190 SW 68th Parkway, Suite 200
Portland, OR 97223-8368

Phone: 503.207.4700

Toll Free: 877.388.8385

infocus.com

© 2016 InFocus Corporation