



**Minature**  
**T&B Catalog Number:**

TY075-18

**UPC Number:**

78621089850

**Status:**

Active

**Description:**

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 91.44mm (3.6 Inches), Width of 2.413mm (0.095 Inches), Thickness of 1.12mm (0.044 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

**Features**

The integrally formed nylon pawl combines low insertion and high locking strength.

**Standards**

UL Listed

**General**

Material Nylon 6.6  
 Color Natural

**Dimension Information**

Nominal Length (inches) 4  
 Length (inches) 3.6  
 Width (inches) 0.100  
 Max. Wire Bundle Diameter (inches) 5/8  
 Min. Wire Bundle Diameter (inches) 1/16

**Specifications**

Temperature Rating -40°F to 185°F  
 Flammability Rating UL 94 V-2

**Tooling**

Application Tools ERG50, QC-100, L-200, L-400-C

**Packaging**

T&B Order Multiple 1000  
 T&B Inner Pack 1000  
 Package in Units 10000  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 0.06 lbs. per 100

**Certifications**

RoHS Compliance Yes

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com