



Heavy Duty Application T&B Catalog Number:

UPC Number:
Status:
Description:

TC92
78621082238
Active

Saddle-Type Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 15.11mm (0.595 Inches), Width of 15.11mm (0.595 Inches), Height of 14.27mm (0.562 Inches), Screw Mounting Method, #6 Screw

Features

Saddle Mounting Plate for use with round bundles.

General

Material	Nylon 6.6
Color	Natural
Mounting Method	Screw
Stud Size	#6 Screw
Max Tie Width Accepted	.19
For Cable Ties	Up to 50 lbs.

Dimension Information

Max. Wire Bundle Diameter (inches)	1.25
------------------------------------	------

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	3.83 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com