




REV.	DESCRIPTION	DATE	APPROVED
E	Engineering Update w/o Changes	03/09/04	M. C.
F	Added Concave Entry Feature	08/26/09	T. Y.
G	Updated General Specifications Note 1.	10/01/12	T. Y.
H	Added Panel Thickness.	05/01/15	J. C.
J	Added Color Options, Sheet #2.	02/02/16	J. C.



Part No.	X = Body Length
PLP5-125	0.125 (3.2mm)
PLP5-250	0.250 (6.4mm)
PLP5-350	0.350 (8.9mm)
PLP5-375	0.375 (9.5mm)
PLP5-500	0.500 (12.7mm)
PLP5-625	0.625 (15.9mm)
PLP5-750	0.750 (19.0mm)
PLP5-1000	1.000 (25.4mm)
PLP5-1250	1.250 (31.8mm)
PLP5-1500	1.500 (38.1mm)



2. MATERIAL: POLYCARBONATE, 94V-0, CLEAR.


1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101 and BSMC-1001.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 <b>TITLE:</b> LIGHT PIPE, PRESS-FIT PANEL MOUNT, ROUND TOP, 5mm	
.XX ± .02			
.XXX ± .010			
DESIGNED: <b>Michael Chen</b>	DATE: <b>01/14/03</b>	<b>PART NO:</b> PLP5-XXX	REVISION: <b>J</b>
CHECKED: <b>D. Green</b>	DATE: <b>01/14/03</b>	<b>CAGE CODE :</b> 32559	<b>SHEET #</b> 1 OF 2
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

**OTHER AVAILABLE COLORS**

\* SEE TABLE FOR ORDERING INFORMATION


REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		



COLOR	Order Code
BLUE	BE
BLACK	BK
GREEN	GN
GRAY	GY
RED	RD
YELLOW	YW

NOTE: LEAVE ORDER CODE BLANK IF NO COLOR IS DESIRED.

3. PARTS ARE DYED TO COLOR UPON REQUEST.

STANDARD TOLERANCE ( UNLESS OTHERWISE SPECIFIED ) <u>DECIMALS</u> <u>ANGULAR</u>		<b>BIVAR</b> <sup>®</sup> 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808    FAX: (949) 951-3974	
			
DESIGNED: <b>K. Aukshunas</b>	DATE: <b>01/22/16</b>	<b>TITLE:</b> LIGHT PIPE, PRESS-FIT PANEL MOUNT, ROUND TOP, 5mm	<b>REVISION:</b> <b>J</b>
CHECKED: <b>J. Chiang</b>	DATE: <b>01/22/16</b>	<b>PART NO:</b> PLP5-XXX	<b>SHEET # 2 OF 2</b>
<small>CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.</small>			