



Detectable
T&B Catalog Number:

TY527M-NDT

UPC Number:

78621099537

Status:

Active

Description:

Detectable Cable Tie, Bright Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 334.57mm (13.172 Inches), Width of 6.86mm (0.27 Inches), Thickness of 1.52mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

Features

Detectable by metal detectors, X-ray equipment, or visual detection.

Stainless Steel locking device.

General

Material Nylon 6.6

Color Blue

Dimension Information

Nominal Length (inches) 13

Length (inches) 13.40

Width (inches) .27

Max. Wire Bundle Diameter (inches) 3.5

Specifications

Temperature Rating -40°F to 185°F

Flammability Rating UL 94 V-2

Tooling

Application Tools ERG, ERG120

Packaging

T&B Order Multiple 50

T&B Inner Pack 50

Package in Units 500

Package Type Regular

T&B Sold in UOM Each

T&B Weight Per UOM 1.31 lbs. per 100

Application Support

MSDS Number sds-00046-tb2

T&B Sales Drawings wsd-000276

Material Selection Guide Available on Website

Certifications

RoHS Compliance Yes

Ty-Rap Certifications Ty-Rap Detectable Cable Ties are a safety and contamination solution for Food & Beverage processing plants and may aid companies in meeting the U.S. Food and Drug Administration (FDA) Hazard Analysis and Critical Control Points (HACCP) safety standards and the European Union (EU) hygiene monitoring regulations.

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com