



**Minature**  
**T&B Catalog Number:**

L-6-18-9-C

**UPC Number:**

72849493367

**Status:**

Active

**Description:**

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 162mm (6.38 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

**General**

Material	Nylon 6.6
Color	Natural

**Dimension Information**

Nominal Length (inches)	6
Length (inches)	6.4
Width (inches)	0.100
Max. Wire Bundle Diameter (inches)	1 3/8
Min. Wire Bundle Diameter (inches)	1 1/16

**Specifications**

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

**Tooling**

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

**Packaging**

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	20000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1.3 lbs. per 1000

**Application Support**

T&B Sales Drawings	wsd-000218
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com