



## Standard Barrel Copper Lug

**T&B Catalog Number:**

54148

**UPC Number:**

78621054148

**Status:**

Active

**Description:**

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, #1 AWG Wire, 3/8" Bolt Size, Tin Plated with Inspection Hole, Green 37

### General

Material	Copper
Finish	Tin Plated
Wire Size	#1 AWG
Number of Studs	1
Stud Size	3/8
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Green
Die Code	37

### Dimension Information

A (inches)	1.78
B (inches)	0.98
C (inches)	0.68
D (inches)	0.11
E (inches)	0.47
F (inches)	3/8

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	3.88 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00675-tb2
Product Overview	Available on Website

### Notes

Dimensions given for reference only. Dimensions may vary up to .030.

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)