



**Standard**  
**T&B Catalog Number:**

TY527M

**UPC Number:**

78621080511

**Status:**

Active

**Description:**

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 340mm (13.4 Inches), Width of 7.0mm (0.27 Inches), Thickness of 1.65mm (0.06 Inches), Tensile Strength Rating of 530 Newtons (120 Pounds)

### Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

### General

Material	Nylon 6.6
Color	Natural

### Dimension Information

Nominal Length (inches)	13
Length (inches)	13.4
Width (inches)	.270
Max. Wire Bundle Diameter (inches)	3.5

### Specifications

Military Standard Part No.	MS3367-3
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

### Tooling

Application Tools	ERG120, WT197
-------------------	---------------

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	1 lbs. per 100

### Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

### Certifications

RoHS Compliance	Yes
UL recognised	No

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com