



Disconnects
T&B Catalog Number:

A18-250A
 78621087901
 Active

UPC Number:
Status:
Description:

Non-Insulated 90 Degree Flag Female Disconnect, Length .58 Inches, Width .61 Inches, Tab Size .250x.032, Wire Range #22-#18 AWG, Copper, Tin Plated

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

General

Disconnect Type	Female - 250 Series Flag
Insulation Type	Non-Insulated
Terminal Series	A
Material	Brass
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	22-18
Tab Size	.250 x .032

Dimension Information

Stock Thickness	.03
A (inches)	.58
B (inches)	.61

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4002

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.37 lbs. per 100
Alternate Package Qty	A252G

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com