



Standard
T&B Catalog Number:

TY5272MX

UPC Number:

78621085544

Status:

Active

Description:

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant Polyamide (Nylon 6.6) for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 222.3mm (8.75 Inches), Width of 6.9mm (0.27 Inches), Thickness of 1.27mm (0.05 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material Nylon 6.6 Weather Resistant
 Color Black

Dimension Information

Nominal Length (inches) 9
 Length (inches) 8.75
 Width (inches) .270
 Max. Wire Bundle Diameter (inches) 2

Specifications

Temperature Rating -40°F to 185°F
 Flammability Rating UL 94 V-2

Tooling

Application Tools ERG120, WT197

Packaging

T&B Order Multiple 50
 T&B Inner Pack 50
 Package in Units 250
 Package Type Regular
 T&B Sold in UOM Each
 T&B Weight Per UOM 10 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com