



**Ring Terminal**  
**T&B Catalog Number:**

RC337  
 78621081979  
 Active

**UPC Number:**  
**Status:**  
**Description:**


Vinyl Insulated Ring Terminal, Length 1.06 Inches, Width .31 Inches, Maximum Insulation .210, Bolt Hole #6, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wire's flex point. Brazed seam barrel is serrated to obtain high pull-out value.



**General**

|                 |                     |
|-----------------|---------------------|
| Insulation Type | Insulated Vinyl     |
| Terminal Series | RC                  |
| Material        | Copper              |
| Finish          | Electro -Tin Plated |
| Color           | Yellow              |
| Wire Range      | 12-10               |
| Stud Size       | #6                  |

**Dimension Information**

|                             |      |
|-----------------------------|------|
| Maximum Insulation (inches) | .210 |
| Stock Thickness             | .04  |
| A (inches)                  | 1.06 |
| B (inches)                  | .31  |
| C (inches)                  | .27  |
| M (inches)                  | .90  |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 105°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

|                   |  |
|-------------------|--|
| Tool Charts       | Available on Website                     |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003 |
| Recommended Tool  | ERG4001                                  |

**Packaging**

|                       |                 |
|-----------------------|-----------------|
| T&B Order Multiple    | 500             |
| T&B Inner Pack        | 500             |
| Package in Units      | 5000            |
| Package Type          | Bulk            |
| T&B Sold in UOM       | Each            |
| T&B Weight Per UOM    | 5 lbs. per 1000 |
| Alternate Package Qty | 10RC-6          |

**Application Support**

|          |                      |
|----------|----------------------|
| Overview | Available on Website |
|----------|----------------------|

Wire Guide Tables

Available on Website

## Notes

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

## Certifications

RoHS Compliance

Yes

## Certifications



File Nbr:

E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com