



**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

**General ordering data**

|                     |  |
|---------------------|--|
| Delivery status     | <b>This article will no longer be available in the future.</b>   |
| Available until     | 2017-12-31   |
| Type                | SL 5.08/04/90B 3.2SN OR BX   |
| Order No.           | <a href="#">1510560000</a>   |
| Version             | PCB plug-in connector, male header, Dovetails for fixing blocks, Solder connection, 5.08 mm, No. of poles: 4, Solder pin length (l): 3.2 mm, tinned, Orange, Box |
| GTIN (EAN)          | 4008190046842  |
| Qty.                | 100 pc(s).   |
| Product data        | IEC: 400 V / 18 A<br>UL: 300 V / 15 A  |
| Packaging           | Box  |
| Alternative product | <a href="#">1148100000</a>   |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 1.36 g

**System parameters**

| Product family                               |                                     | Mounting onto the PCB                      |                       |
|--|-------------------------------------|--|-----------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08 |  | Solder connection     |
| Pitch in mm (P)                              | 5.08 mm                             | Pitch in inches (P)                        | 0.2 inch              |
| No. of poles                                 | 4                                   | Solder pin length (l)                      | 3.2 mm                |
| Solder pin length tolerance                  | +0.1 / -0.3 mm                      | Solder pin dimensions                      | d = 1.2 mm, Octagonal |
| Solder pin dimensions = d tolerance          | 0 / -0.03 mm                        | Plugging cycles                            | 25                    |
| Can be coded                                 | Yes                                 | Number of solder pins per pole             | 1                     |
| Solder eyelet hole diameter (D)              | 1.3 mm                              | Solder eyelet hole diameter tolerance (D)  | + 0,1 mm              |
| L1 in mm                                     | 15.24 mm                            | L1 in inches                               | 0.6 inch              |
| Insulation resistance                        | ≥ 10 <sup>8</sup> Ω                 | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged          |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch, plugged     | Volume resistance                          | 4.50 mΩ               |


**Material data**

|                                       |        |                                       |                            |
|---------------------------------------|--------|---------------------------------------|----------------------------|
| Insulating material                   | PBT    | Moisture Level (MSL)                  | 3                          |
| Colour                                | Orange | Insulating material group             | IIIa                       |
| UL 94 flammability rating             | V-0    | CTI                                   | ≥ 200                      |
| Contact material                      | CuSn   | Layer structure of solder connection  | 2-3 μm Ni / 2-4 μm Sn matt |
| Contact surface                       | tinned | Operating temperature, min.           | -50 °C                     |
| Operating temperature, max.           | 100 °C | Temperature range, installation, min. | -25 °C                     |
| Temperature range, installation, max. | 100 °C | Storage temperature, min.             | -25 °C                     |
| Storage temperature, max.             | 55 °C  | Max. relative humidity during storage | 80 %                       |

**Rating data acc. to IEC 60664-1 / IEC 61984**

|  |                   |   |        |
|--|-------------------|---|--------|
| Rated current, min. no. of poles (Ta = 20°C)                   | 18 A              | Rated current, max. no. of poles (Ta = 20°C)                              | 14.5 A |
| Rated current, min. no. of poles (Ta = 40°C)                   | 15 A              | Rated current, max. no. of poles (Ta = 40°C)                              | 12 A   |
| Rated voltage for surge voltage class / pollution degree III/3 | 250 V             | Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV   |
| Rated voltage for surge voltage class / pollution degree III/2 | 320 V             | Rated impulse voltage for surge voltage class/ pollution degree III/2     | 4 kV   |
| Rated voltage for surge voltage class / pollution degree II/2  | 400 V             | Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV   |
| Short-time withstand current resistance                        | 3 x 1s with 120 A |   |        |

**Rated data acc. to CSA**

|                              |   |                             |                |
|------------------------------|---|-----------------------------|----------------|
| Institute (CSA)              |  | Certificate No. (CSA)       | 200039-1121690 |
| Rated voltage (Use group B)  | 300 V   | Rated voltage (use group D) | 300 V          |
| Rated current (use group B)  | 15 A  | Rated current (use group D) | 10 A           |
| Reference to approval values | Specifications are maximum values, details - see approval certificate.              |                             |                |

## Data sheet

### OMNIMATE Signal - series BL/SL 5.08 SL 5.08/04/90B 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Rated data acc. to UL 1059

Institute (UR)



Certificate No. (UR)

E60693

|                              |  |
|------------------------------|--|
| Rated voltage (use group B)  | 300 V  |
| Rated current (use group B)  | 15 A   |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. |

|                             |       |
|-----------------------------|-------|
| Rated voltage (use group D) | 300 V |
| Rated current (use group D) | 10 A  |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001284    | ETIM 4.0   | EC002637    |
| ETIM 5.0   | EC002637    | ETIM 6.0   | EC002637    |
| UNSPSC     | 30-21-18-10 | eClass 5.1 | 27-26-07-04 |
| eClass 6.2 | 27-26-07-04 | eClass 7.1 | 27-44-04-02 |
| eClass 8.1 | 27-44-04-02 | eClass 9.0 | 27-44-04-02 |

### Notes

Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

IPC conformity

The products are developed, manufactured and delivered according to the internationally recognised IPC-A-610 standard, category "permissible". More extensive demands on the products can be evaluated on request.

### Approvals

Approvals



ROHS

Conform

### Downloads


CAD Library (P-CAD Format - ASCII) [SL.zip](#)  
 CAD Library (P-CAD Format - Standard) [SL.zip](#)  
[3-D model](#)

**Data sheet**

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**



**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**
**BLF 5.08HC/180 SN**


Just as reliable as the millionfold proven original and featuring innovative details:  
The BLF 5.08HC PUSH IN version of the BLZP 5.08HC female connector is not only different in terms of connection system; it also has a more compact design. Weidmüller's innovative PUSH IN spring connection system stands for the future of easy and tool-free wire connection. HC = High Current.  
In terms of versatility, the BLF 5.08HC offers just as much as the version which served as a model:

- 3 tested-and-proven wire outlet directions provide the usual flexibility for application-specific design
- 4 flange variations and the patented release latch allow the locking concept to be based on the requirements of the user
- Use the BLF 5.08HC and SL 5.08HC plug combination to reach the max. rated specifications

**General ordering data**

| Type                             | Order No.                  | Version  | GTIN (EAN)      | Qty.   | Product data   | Packaging |
|----------------------------------|----------------------------|--|-----------------|--------|--|-----------|
| BLF<br>5.08HC/04/180<br>SN OR BX | <a href="#">1013710000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 180°, PUSH<br>IN, Clamping range, rated<br>connection, max.: 3.31<br>mm <sup>2</sup> , Box | 403224872182590 | pc(s). | IEC: 400 V / 24 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 18.5 A / AWG 26 - AWG<br>12 | Box       |

**BLL 5.08/180**


Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

**General ordering data**

| Type                               | Order No.                  | Version   | GTIN (EAN)      | Qty.   | Product data                          | Packaging |
|------------------------------------|----------------------------|---|-----------------|--------|---------------------------------------|-----------|
| BLL<br>5.08/04/180<br>3.2 SN OR BX | <a href="#">1630730000</a> | PCB plug-in connector,<br>female header, closed side,<br>Solder connection, 5.08<br>mm, No. of poles: 4, 180°,<br>Solder pin length (l): 3.2<br>mm, tinned, Orange, Box | 400819020415090 | pc(s). | IEC: 400 V / 23 A<br>UL: 300 V / 15 A | Box       |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**

**BLZ 5.08/180**



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status Available until  | Type                     | Order No.                  | Version   | GTIN (EAN)    | Qty.       |
|--|--------------------------|----------------------------|---|---------------|------------|
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180 SN BK BX | <a href="#">1526610000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm², Box | 4008190049454 | 100 pc(s). |
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180 SN OR BX | <a href="#">1526660000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm², Box | 4008190148232 | 100 pc(s). |

**BLZ 5.08/225**



Female plugs with clamping-yoke screw for wire connection with 225° outlet direction. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status Available until  | Type                     | Order No.                  | Version   | GTIN (EAN)    | Qty.      |
|--|--------------------------|----------------------------|---|---------------|-----------|
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BLZ 5.08/04/225 SN BK BX | <a href="#">1741890000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, | 4008190254155 | 90 pc(s). |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**

225°, Clamping  
yoke connection,  
Clamping range,  
rated connection,  
max.: 3.31 mm²,  
Box

|   |                           |                          |                            |   |               |           |
|---|---------------------------|--------------------------|----------------------------|---|---------------|-----------|
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/225 SN OR BX | <a href="#">1741660000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm², Box | 4008190202637 | 90 pc(s). |
|   |                           |                          |                            |   |               |           |

**BLZF 5.08/90**



Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status   | Available until           | Type                     | Order No.                  | Version  | GTIN (EAN)    | Qty.      |
|---|---------------------------|--------------------------|----------------------------|--|---------------|-----------|
| This article will no longer be available in the future. | 2015-12-31T00:00:00+01:00 | BLZF 5.08/04/90 SN BK BX | <a href="#">1671040000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm², Box | 4008190432713 | 90 pc(s). |
|   |                           |                          |                            |  |               |           |
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZF 5.08/04/90 SN OR BX | <a href="#">1670810000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm², Box | 4008190432416 | 90 pc(s). |
|   |                           |                          |                            |  |               |           |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**
**BLL 5.08/90**


Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

**General ordering data**

| Type                              | Order No.                  | Version  | GTIN (EAN)      | Qty.   | Product data                          | Packaging |
|-----------------------------------|----------------------------|--|-----------------|--------|---------------------------------------|-----------|
| BLL<br>5.08/04/90<br>3.2 SN OR BX | <a href="#">1622960000</a> | PCB plug-in connector,<br>female header, closed side,<br>Solder connection, 5.08<br>mm, No. of poles: 4, 90°,<br>Solder pin length (l): 3.2<br>mm, tinned, Orange, Box | 400819019402490 | pc(s). | IEC: 400 V / 23 A<br>UL: 300 V / 15 A | Box       |

**BLZF 5.08/270**


Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status Available until                         | Type                      | Order No.                  | Version  | GTIN (EAN)    | Qty.      |
|---|---------------------------|----------------------------|--|---------------|-----------|
| This article will no longer be available in the future. | BLZF 5.08/04/270 SN BK BX | <a href="#">1672190000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 270°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190433901 | 90 pc(s). |
| This article will no longer be available in the future. | BLZF 5.08/04/270 SN OR BX | <a href="#">1671960000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 270°, Tension clamp connection, Clamping range, rated connection,                                  | 4008190433673 | 90 pc(s). |



**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**

max.: 3.31 mm<sup>2</sup>,  
Box

**BLZP 5.08HC/270 SN**


Female plugs with clamping-yoke connection for connecting wires with a right-angle (90° or 270°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

**General ordering data**

| Type                              | Order No.                  | Version  | GTIN (EAN)              | Qty. | Product data  | Packaging |
|-----------------------------------|----------------------------|--|-------------------------|------|---|-----------|
| BLZP<br>5.08HC/04/270<br>SN OR BX | <a href="#">1948810000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 270°, Clamping<br>yoke connection, Clamping<br>range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box | 4032248626267 90 pc(s). |      | IEC: 400 V / 23 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 20 A / AWG 30 - AWG 12 | Box       |
| BLZP<br>5.08HC/04/270<br>SN BK BX | <a href="#">1949040000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 270°, Clamping<br>yoke connection, Clamping<br>range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box | 4032248626496 90 pc(s). |      | IEC: 400 V / 23 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 20 A / AWG 30 - AWG 12 | Box       |

**BLT 5.08HC**


Female plugs with TOP screw connection system for connecting wires with straight 180° outlet direction. The female connectors provide space for labelling and can be coded. HC = High Current.

**General ordering data**

| Type                             | Order No.                  | Version  | GTIN (EAN)              | Qty. | Product data  | Packaging |
|----------------------------------|----------------------------|--|-------------------------|------|---|-----------|
| BLT<br>5.08HC/04/180<br>SN BK BX | <a href="#">1499710000</a> | PCB plug-in connector,<br>female plug, 5.08 mm,<br>No. of poles: 4, 180°, TOP<br>connection, Clamping<br>range, rated connection,<br>max.: 2.5 mm <sup>2</sup> , Box | 4008190861711 90 pc(s). |      | IEC: 400 V / 27 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 17 A / AWG 26 - AWG 14 | Box       |
| BLT<br>5.08HC/04/180<br>SN OR BX | <a href="#">1499760000</a> | PCB plug-in connector,<br>female plug, 5.08 mm,<br>No. of poles: 4, 180°, TOP  | 4008190037536 90 pc(s). |      | IEC: 400 V / 27 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 17 A / AWG 26 - AWG 14 | Box       |

Creation date February 19, 2016 9:52:43 AM CET

## OMNIMATE Signal - series BL/SL 5.08 SL 5.08/04/90B 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Mating connector (conditionally pluggable)

connection, Clamping  
range, rated connection,  
max.: 2.5 mm<sup>2</sup>, Box

#### BLZP 5.08HC/180 SN




Female plug with clamping-yoke screw system for connecting wires with straight (180°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

#### General ordering data

| Type                              | Order No.                  | Version  | GTIN (EAN)    | Qty.      | Product data  | Packaging |
|-----------------------------------|----------------------------|--|---------------|-----------|---|-----------|
| BLZP<br>5.08HC/04/180<br>SN BK BX | <a href="#">1943830000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 180°, Clamping<br>yoke connection, Clamping<br>range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box | 4032248617869 | 90 pc(s). | IEC: 400 V / 23 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 20 A / AWG 30 - AWG 12 | Box       |
| BLZP<br>5.08HC/04/180<br>SN OR BX | <a href="#">1943600000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 180°, Clamping<br>yoke connection, Clamping<br>range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box | 4032248617593 | 90 pc(s). | IEC: 400 V / 23 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 20 A / AWG 30 - AWG 12 | Box       |

#### BLC 5.08R



Female plugs with crimp wire connection system. The female plugs provide space for labelling and can be coded.

#### General ordering data

| Type                         | Order No.                  | Version  | GTIN (EAN)    | Qty.       | Product data  | Packaging |
|------------------------------|----------------------------|--|---------------|------------|---|-----------|
| BLC<br>5.08/04/180R<br>BK BX | <a href="#">1711980000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 180°, Crimp<br>connection, Clamping<br>range, rated connection,<br>max.: 2.5 mm <sup>2</sup> , Box | 4008190934996 | 100 pc(s). | IEC: 400 V / 21 A<br>UL: 300 V / 10 A / AWG 26 - AWG 14 | Box       |

Creation date February 19, 2016 9:52:43 AM CET

## OMNIMATE Signal - series BL/SL 5.08 SL 5.08/04/90B 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Mating connector (conditionally pluggable)

|                              |                            |  |                          |   |     |
|------------------------------|----------------------------|--|--------------------------|---|-----|
| BLC<br>5.08/04/180R<br>OR BX | <a href="#">1610510000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 180°, Crimp<br>connection, Clamping<br>range, rated connection,<br>max.: 2.5 mm <sup>2</sup> , Box | 4008190065102 100 pc(s). | IEC: 400 V / 21 A<br>UL: 300 V / 10 A / AWG 26 - AWG 14 | Box |
|------------------------------|----------------------------|--|--------------------------|---|-----|

### BL 5.08



Female plugs with leaf-spring wire connection system.  
 The female plugs provide space for labelling.

### General ordering data

| Delivery status Available until  | Type                        | Order No.                  | Version  | GTIN (EAN)    | Qty.          |
|--|-----------------------------|----------------------------|--|---------------|---------------|
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BL 5.08/04/180 SN DKG<br>BX | <a href="#">1723850000</a> | PCB plug-in<br>connector, female<br>plug, 5.08 mm,<br>No. of poles: 4,<br>180°, Pressure<br>clamp connection,<br>Clamping range,<br>rated connection,<br>max.: 2.08 mm <sup>2</sup> ,<br>Box | 4008190376215 | 100<br>pc(s). |
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BL 5.08/04/180 SN OR BX     | <a href="#">1716340000</a> | PCB plug-in<br>connector, female<br>plug, 5.08 mm,<br>No. of poles: 4,<br>180°, Pressure<br>clamp connection,<br>Clamping range,<br>rated connection,<br>max.: 2.08 mm <sup>2</sup> ,<br>Box | 4008190376376 | 100<br>pc(s). |
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BL 5.08/04/180 SN BK BX     | <a href="#">1716490000</a> | PCB plug-in<br>connector, female<br>plug, 5.08 mm,<br>No. of poles: 4,<br>180°, Pressure<br>clamp connection,<br>Clamping range,<br>rated connection,<br>max.: 2.08 mm <sup>2</sup> ,<br>Box | 4008190376536 | 100<br>pc(s). |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**
**BLZ 5.08/270**


Female plugs with clamping-yoke screw connection. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status   | Available until           | Type                     | Order No.                  | Version  | GTIN (EAN)    | Qty.      |
|---|---------------------------|--------------------------|----------------------------|--|---------------|-----------|
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/270 SN OR BX | <a href="#">1557560000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190104788 | 90 pc(s). |
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/270 SN BK BX | <a href="#">1557510000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190269449 | 90 pc(s). |

**BLZP 5.08HC/225 SN**


Clamping-yoke connection with right-angled (90° or 270°) or angled (225°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

**General ordering data**

| Type                        | Order No.                  | Version  | GTIN (EAN)   | Qty.       | Product data  | Packaging |
|-----------------------------|----------------------------|--|--------------|------------|---|-----------|
| BLZP 5.08HC/04/225 SN BK BX | <a href="#">1946580000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 225°, Clamping yoke connection, Clamping | 403224862235 | 190 pc(s). | IEC: 400 V / 17.5 A / 0.2 - 4 mm <sup>2</sup><br>UL: 300 V / 15 A / AWG 30 - AWG 12 | Box       |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**

|                                   |                            |  |                        |   |
|-----------------------------------|----------------------------|--|------------------------|---|
|                                   |                            | range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box  |                        |   |
| BLZP<br>5.08HC/04/225<br>SN OR BX | <a href="#">1946270000</a> | PCB plug-in connector,<br>female plug, 5.08 mm, No.<br>of poles: 4, 225°, Clamping<br>yoke connection, Clamping<br>range, rated connection,<br>max.: 4 mm <sup>2</sup> , Box | 403224862184290 pc(s). | IEC: 400 V / 17.5 A / 0.2 - 4 mm <sup>2</sup> Box<br>UL: 300 V / 15 A / AWG 30 - AWG 12 |

**BLZ 5.08 QV2**


Female plugs with clamping-yoke screw connections for connecting wire, with straight 180° wire outlet direction and internal cross-connections between connections 1-2 and 3-4. Bus current at 4 mm<sup>2</sup> (without wire-end ferrule) is up to 32 A. The female plugs can be coded.

**General ordering data**

| Delivery status   | Available until           | Type                            | Order No.                  | Version   | GTIN (EAN)    | Qty.      |
|---|---------------------------|---------------------------------|----------------------------|---|---------------|-----------|
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180QV2 SN BK BX PRT | <a href="#">1839780000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm <sup>2</sup> , Box | 4032248350308 | 90 pc(s). |
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180QV2 SN OR BX PRT | <a href="#">1839770000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm <sup>2</sup> , Box | 4032248350292 | 90 pc(s). |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmuller.com

**Mating connector (conditionally pluggable)**
**BLZ 5.08F QV2**


Female plugs with clamping-yoke screw connections for connecting wire, with straight 180° wire outlet direction and internal cross-connections between connections 1-2 and 3-4. Bus current at 4 mm<sup>2</sup> (without wire-end ferrule) is up to 32 A. The female plugs can be coded.

**General ordering data**

| Delivery status   | Available until           | Type                             | Order No.                  | Version   | GTIN (EAN)    | Qty.      |
|---|---------------------------|----------------------------------|----------------------------|---|---------------|-----------|
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180FQV2 SN OR BX PRT | <a href="#">1846870000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm <sup>2</sup> , Box | 4032248362684 | 60 pc(s). |
| This article will no longer be available in the future. | 2017-12-31T00:00:00+01:00 | BLZ 5.08/04/180FQV2 SN BK BX PRT | <a href="#">1844500000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm <sup>2</sup> , Box | 4032248354948 | 60 pc(s). |

**BLIDC 5.08**


Female plugs with IDC wire connection system. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Available until           | Type                       | Order No.                  | Version  | GTIN (EAN)    | Qty.       | Product data        |
|---------------------------|----------------------------|----------------------------|--|---------------|------------|---------------------|
| 2011-11-17T00:00:00+01:00 | BLIDC 5.08/04/180 SN OR BX | <a href="#">1724960000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180° | 4008190377304 | 100 pc(s). | IEC: 400 V / 11 A / |

**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (conditionally pluggable)**

|                              |  |
|------------------------------|--|
| IDC terminal,                | 0.5  |
| Clamping range,              | -  |
| rated connection,            | 0.75   |
| max.: 0.75 mm <sup>2</sup> , | mm <sup>2</sup>  |
| Box                          | UL:<br>300<br>V /<br>5<br>A /<br>AWG<br>22<br>-<br>AWG<br>20 |

**BLZ 5.08/90**




Female plugs with clamping-yoke screw connection. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status Available until  | Type                    | Order No.                  | Version   | GTIN (EAN)    | Qty.      |
|--|-------------------------|----------------------------|---|---------------|-----------|
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BLZ 5.08/04/90 SN OR BX | <a href="#">1552960000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190123932 | 90 pc(s). |
| This article will no longer be available in the future.<br>2017-12-31T00:00:00+01:00 | BLZ 5.08/04/90 SN BK BX | <a href="#">1552910000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190267728 | 90 pc(s). |

**OMNIMATE Signal - series BL/SL 5.08**  
**SL 5.08/04/90B 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (conditionally pluggable)**
**BLDT 5.08**


Female plugs with two clamping-yoke screw connections per pole for wire connections with 90° and 270° outlet directions. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Type                          | Order No.                  | Version   | GTIN (EAN)    | Qty.      | Product data  | Packaging |
|-------------------------------|----------------------------|---|---------------|-----------|---|-----------|
| BLDT<br>5.08/04/- SN<br>BK BX | <a href="#">1660730000</a> | PCB plug-in connector,<br>female plug, 5.08 mm,<br>No. of poles: 4, 180°, TOP<br>connection, Clamping<br>range, rated connection,<br>max.: 3.31 mm <sup>2</sup> , Box | 4008190417185 | 75 pc(s). | IEC: 400 V / 14 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 10 A / AWG 26 - AWG 12 | Box       |
| BLDT<br>5.08/04/- SN<br>OR BX | <a href="#">1644750000</a> | PCB plug-in connector,<br>female plug, 5.08 mm,<br>No. of poles: 4, 180°, TOP<br>connection, Clamping<br>range, rated connection,<br>max.: 3.31 mm <sup>2</sup> , Box | 4008190283964 | 75 pc(s). | IEC: 400 V / 14 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 10 A / AWG 26 - AWG 12 | Box       |

**BLZF 5.08/180**


Female plugs with tension-clamp wire connection system, straight 180° outlet direction. The female plugs provide space for labelling and can be coded.

**General ordering data**

| Delivery status Available until                         | Type                      | Order No.                  | Version  | GTIN (EAN)    | Qty.      |
|---|---------------------------|----------------------------|--|---------------|-----------|
| This article will no longer be available in the future. | BLZF 5.08/04/180 SN BK BX | <a href="#">1707710000</a> | PCB plug-in connector, female plug, 5.08 mm, No. of poles: 4, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm <sup>2</sup> , Box | 4008190316716 | 90 pc(s). |



## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

# Addresses worldwide




Let's connect.

- AE United Arab Emirates**  
Weidmüller Middle East FZE  
Warehouse Q3-79  
SAIF-Zone  
P.O. BOX 8591  
Sharjah  
Telephone number +971 65572723  
Fax number +971 65572724  
wme.info@weidmueller.com
- AO Angola**  
Please contact  
Phambili Interface  
South Africa
- AR Argentina**  
CPI SA  
Bauness 2660  
C1431DOF Buenos Aires  
Telephone number +54 11 4523 8008  
Fax number +54 11 4522 0546  
info@cpi.com.ar  
www.cpi.com.ar
- AT Austria**  
Weidmüller GmbH  
IZ NOE Süd Straße 2b, Obj  
M 59  
2355 Wiener Neudorf  
Telephone number +43 2236 67080  
Fax number +43 2236 6708-899  
office.at@weidmueller.com  
www.weidmueller.com
- AU Australia**  
Weidmüller Pty. Ltd.  
PO BOX 6944  
Huntingwood 2148  
Huntingwood Drive 43  
Huntingwood NSW 2148  
Telephone number +61 2 9671 9999  
Fax number +61 2 9671 9911  
info@weidmuller.com.au  
www.weidmuller.com.au
- AZ Azerbaijan**  
Representative Office  
Weidmüller Interface  
Demirchi Tower, 4th floor  
37, Khojali ave.  
AZ 1025 Baku  
Telephone number +994 12 488 80 36  
Fax number +994 12 488 80 37  
rashad.mahmudov@weidmueller.com
- BA Bosnia and Herzegovina**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia  
  
or  
  
BIG electric d.o.o  
Mladena Stojanovića 117A  
78000 Banja Luka  
Telephone number +387 51926277  
Fax number +387 51926277  
bigelectric@blic.net  
www.bigelectric.ba
- BE Belgium**  
Weidmüller Benelux B. V.  
Mechelsesteenweg 519 bus  
6 an 7  
1930 Nossegem  
Telephone number +32 2 752 40 70  
Fax number +32 2 751 36 06  
info@weidmueller.be  
www.weidmueller.be
- BG Bulgaria**  
Weid-Bul EOOD  
Bul. "Kliment Ohridski" 13  
1756 Sofia  
Telephone number +359 2 963 2560  
Fax number +359 2 963 1098  
sofia@weidbul.com  
www.weidbul.com
- BH Bahrain**  
Khayber Trading Company  
P.O Box 1976  
Manama  
Telephone number +973 720747  
Fax number +973 720331  
khayber@batelco.com.bh
- BR Brazil**  
Weidmüller Conexel do Brasil  
Conexões Elétricas Ltda.  
Av. Presidente Juscelino, 642  
- Piraporinha  
Diadema, São Paulo  
09950-370  
Telephone number +55 (11) 4366-9600  
Fax number +55 (11) 4362-1677  
vendas@weidmueller.com.br  
www.weidmueller.com.br
- BW Botswana**  
Please contact  
Phambili Interface  
South Africa
- BY Belarus**  
TECHNIKON Ltd.  
Nezavisimosti pr. 177-9  
220125 Minsk  
Telephone number +375 17 393-11-77  
Fax number +375 17 3930080  
wm@technikon.by
- CA Canada**  
W Interconnections Canada  
Inc.  
10 Spy Court  
Markham Ontario L3R 5H6  
Telephone number +1 (905) 475-1507 Ext. 9836  
Fax number +1 (905) 475-2798  
support@weidmuller.ca  
www.weidmuller.ca
- CG Congo**  
Please contact  
Phambili Interface  
South Africa
- CH Switzerland**  
Weidmüller Schweiz AG  
Rundbuckstraße 2  
82 12 Neuhausen am  
Rheinfall SH  
Telephone number +41 52 674 07 07  
Fax number +41 52 674 07 08  
info@weidmueller.ch  
www.weidmueller.ch
- CL Chile**  
ATS - INTECH  
María Luisa Santander 0475  
Santiago  
Providencia 7500859  
Telephone number +56 2 341 1271  
Fax number +56 2 341 1275  
felipe@atsintech.com  
www.atsintech.com  
  
CPI CHILE LTDA  
Av. Presidente Frei Montalva  
6001, 47 complejo el cortijo  
Santiago - Conchalí  
Telephone number +562 963 8440  
Fax number +562 963 8440  
cpi@cpichile.cl  
www.cpichile.cl
- CN China**  
Weidmüller Interface  
(Shanghai) Co. Ltd.  
100 Yutong Road  
25 F, BM Intercontinental  
Business Center  
200070 Shanghai  
Telephone number +86 21-22195008  
Fax number +86 21-22195009  
customer.hotline@weidmueller.com.cn  
www.weidmueller.com.cn
- CO Colombia**  
Automatización Avanzada  
S. A.  
Carrera 97 No., 24 c - 23  
Bodega 4  
110911 Bogotá-D.C.  
Telephone number +57 (1) 547-8510  
Fax number +57 (1) 422-3044  
comercial@automatizacionavanzada.com  
www.automatizacionavanzada.com
- CR Costa Rica**  
ELVATRON S. A.  
la Uruca 400 Norte Banco  
Costa Rica  
San Jose Costa Rica  
Telephone number +506 2961-060  
Fax number +506 5200-609  
dirk.haase@elvatron.com  
www.elvatron.com
- CZ Czech Republic**  
Weidmüller s.r.o.  
Lomnického 5/1705  
140 00 Praha 4  
Telephone number +420 244 001 400  
Fax number +420 244 001 499  
office@weidmueller.cz  
www.weidmueller.cz
- DE Germany**  
Weidmüller GmbH & Co. KG  
Ohmstraße 9  
32758 Detmold  
Postfach 30 54  
32720 Detmold  
Telephone number +49 5231 1428-0  
Fax number +49 5231 14-292083  
weidmuller@weidmueller.de  
www.weidmueller.de
- DK Denmark**  
Weidmüller Danmark  
Vallensbækvej 18A  
2605 Brøndby  
Telephone number +45 27747800  
kundeservice@weidmuller.dk  
www.weidmuller.dk
- DZ Algeria**  
SARL INTER ELECTRIC  
1a Angles des Rues Okba Ibn  
Nafaa et Hassi Beida  
2300 Annaba  
Telephone number  
Fax number  
contact@inter-electric.com
- EC Ecuador**  
Elsystec S. A., Electricidad  
Sistemas y Tecnología  
Vasco de Contreras N35-251 y  
Mañosa  
Quito - Pichincha  
Telephone number +593 22456510  
Fax number +593 22456755  
Elsystec@uio.satnet.net
- EE Estonia**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Latvia  
  
or  
  
Soots Interface OÜ  
Pärnu mnt 142  
11317 Tallinn  
Telephone number +372 609 6933  
Fax number  
info@sootsinterface.ee  
www.sootsinterface.ee
- EG Egypt**  
Standard Electric (OMEGA)  
1, Abdelhamid Badawy Street  
Heliopolis  
Cairo  
Telephone number +202 21805600  
stdelec@rite.com
- ES Spain**  
Weidmüller, S. A.  
Narcís Monturiol 11-13, Pol.  
Ind. Sudoeste  
8960 Sant Just  
Desvern - Barcelona  
Telephone number +34 934 803 386  
Fax number +34 933 718 055  
weidmuller@weidmuller.es  
www.weidmuller.es
- FI Finland**  
Weidmüller Suomi,  
Weidmüller Aktiebolagetin  
sivuliike  
Koy Plaza Vivace  
Äyritie 8C  
FI 1510 Vantaa  
Telephone number +358 20 7351300  
Fax number +358 800 114 667  
asiakaspalvelu@weidmuller.fi  
www.weidmuller.fi
- FR France**  
Weidmüller E. U. R. L.  
12, Chaussée Jules César  
BP 263 Osny  
95523 Cergy-Pontoise Cedex  
Telephone number +33 1 34 24 55 00  
Fax number +33 1 34 24 55 01  
mail@weidmuller.fr
- GB Great Britain**  
Weidmüller Ltd.  
Klippon House  
Centurion Court Office Park,  
Meridian East, Meridian  
Business Park  
Leicester  
LE19 1TP  
Telephone number +44 116 282 3470  
Fax number +44 116 289 3582  
marketing@weidmuller.co.uk  
www.weidmuller.co.uk
- GE Georgia**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- GH Ghana**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.
- GR Greece**  
G.A. Solutions  
Ippokratous 11 Metamorfosi  
144 52 Athen  
Telephone number +30 210 2823233  
Fax number +30 210 2823233  
info@weidmuller.gr  
www.weidmuller.gr
- GT Guatemala**  
Prestelectro, Prestegard  
Electro, S.A.  
Avenida Petapa 44-22,  
Zona 12  
Guatemala City  
Telephone number +502 2442-3346  
Fax number +502 2476-8945  
ventas@prestelectro.com
- HK Hong Kong**  
Weidmüller (Hong Kong)  
Limited Co. Ltd.  
Unit 1617, Metropolis Tower  
No. 10 Metropolis Drive,  
Hunghom, Kowloon  
Telephone number +852 3154 8088  
Fax number +852 31548099  
Info-hk@weidmueller.com.hk
- HR Croatia**  
ElektroPARTNER d.o.o.  
Slavonska avenija 24/6  
HR-10000 Zagreb  
Telephone number +385 (1) 6184 793  
Fax number +385 (1) 6184 795  
elektropartner@zg.t-com.hr  
www.elektropartner.hr
- HU Hungary**  
Weidmüller Kereskedelmi Kft.  
Budapest  
Gubacsi út 6.  
1097  
Telephone number +36 1 382 7700  
Fax number +36 1 382 7701  
info@weidmueller.hu  
www.weidmueller.hu
- ID Indonesia**  
PT. Nego Electrindo  
Ruko Mega Grosir Cempaka  
Mas Blok I No. 20 – 22  
Jakarta 10640  
Telephone number +62 21 42882255  
Fax number +62 21 42882266  
sales@negoelectrindo.co.id
- IE Ireland**  
Please contact  
Weidmüller Ltd.  
Great Britain
- IL Israel**  
A. U. Shay Ltd.  
23/25, Embarr Street  
49222 Petach-Tikva  
P.O. Box 1 00 49  
49222 Petach-Tikva  
Telephone number +972 3-923-3601  
Fax number +972 3-923-4601  
shay@uriel-shay.com  
www.uriel-shay.com  
  
ATEKA Ltd.  
4, Ha Tavor lane Industrial  
area Segula  
49691 Petach-Tikva  
P.O. Box 4710  
Petach-Tikva  
Telephone number +972 73-200-1311  
Fax number +972 3-924 4245  
marketing@ateka.co.il  
www.ateka.co.il
- IN India**  
Representative Office  
Weidmüller Electronics India  
Pvt. Ltd.  
12th Lane North Avenue, Opp  
Joggers Park,  
Kalyani Nagar, Pune  
411 006  
Telephone number +91 20-41290090  
wmi@weidmueller.in  
www.weidmueller.com
- IS Iceland**  
Samey Automation Center  
Lingsay 13  
210 Garoabaer  
Telephone number +354 510 5200  
Fax number +354 510 5201  
Samey@samey.is  
www.samey.is
- IT Italy**  
Weidmüller S. r.l.  
Via Albert Einstein 4  
20092 Cinisello  
Balsamo Milano  
Telephone number +39 02 660681  
Fax number +39 02 6124945  
weidmuller@weidmuller.it  
www.weidmuller.it
- JM Jamaica**  
Please contact  
W Interconnections Inc.  
United States
- JO Jordan**  
Trans Jordan for Electro  
PO Box 33 06 07  
Amman  
Telephone number +962 6 533 2020  
Fax number +962 6 533 5800  
transjordan@batelco.jo



You can find all Weidmüller addresses and your local contact on the internet at: [www.weidmueller.com/countries](http://www.weidmueller.com/countries)

Let's connect.

Sales company   
Representation abroad   
without representation abroad 

- JP Japan**  
Nihon Weidmüller Co. Ltd.  
Sphere Tower Tennoz 2-2-8  
Higashi-Shinagawa,  
Shinagawa-ku  
Tokyo  
140-0002  
Telephone number +81 3  
6711 5300  
Fax number +81 3 6711  
5333  
[weidmullerjapan@weidmueller.co.jp](mailto:weidmullerjapan@weidmueller.co.jp)  
[www.weidmueller.co.jp](http://www.weidmueller.co.jp)
- KE Kenya**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.
- KG Kyrgyzstan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- KR Korea**  
Weidmüller Korea Co. Ltd.  
9th floor  
429, Teheran-ro, Gangnam-Gu  
Seoul 135-721  
Telephone number +82  
2-516-0003  
Fax number +82 2-516-0090  
[info@weidmueller.co.kr](mailto:info@weidmueller.co.kr)  
[www.weidmueller.co.kr](http://www.weidmueller.co.kr)
- KW Kuwait**  
Kana Controls General Trading  
& Contracting Co. W. L. L.  
Al Rai Industrial Area, Plot  
28-30, St. 31  
13016 Safat  
B.P. 25593  
Telephone number +965  
4741373  
Fax number +965 4741537  
[info@kanacontrols.com](mailto:info@kanacontrols.com)
- KZ Kazakhstan**  
Please contact  
Weidmüller Group  
Russia
- LB Lebanon**  
Progress Engineering &  
Trading Enterprises  
Al Nahr Street  
Beirut 11-1111  
Telephone number +961 1  
444 664  
Fax number +961 1 561 880  
[progress@inco.com.lb](mailto:progress@inco.com.lb)
- LT Lithuania**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Latvia  
  
or  
ELEKTROS IRANGA  
Tinklu g. 29 a  
LT-5319 Panevezys  
Telephone number +370 (45)  
582 828  
Fax number  
[info@eliranga.lt](mailto:info@eliranga.lt)
- LU Luxembourg**  
Please contact  
Weidmüller Benelux B. V.  
Netherlands
- LV Latvia**  
SIA Abi4  
Daugavgrivas 31b  
Rīga, LV-1007  
Telephone number +371 674  
70999  
Fax number +371 674  
24562  
[abi\\_4@tvnet.lv](mailto:abi_4@tvnet.lv)  
  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Udens str. 12-118  
Rīga, LV-1007  
Telephone number +371  
29254766  
Fax number +371 674  
65637  
[ilgonis.rudaks@weidmueller.com](mailto:ilgonis.rudaks@weidmueller.com)  
[www.weidmueller.com](http://www.weidmueller.com)
- MA Morocco**  
Sofimed  
137, Bd Moulay Ismail Roches  
Noires  
20290 Casablanca  
Telephone number  
Fax number  
[contact@sofimedmaroc.com](mailto:contact@sofimedmaroc.com)
- MD Moldova**  
BERHORD A & D srl  
79/1, str. Milescu Spartaru  
MD-2075 Chisinau  
Moldova  
Telephone number +373 (22)  
815002  
Fax number +373 (22)  
815007  
[atuleanu@berhord.com](mailto:atuleanu@berhord.com)  
[www.ad.berhord.com](http://www.ad.berhord.com)
- ME Montenegro**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia.
- MG Madagascar**  
Please contact  
Phambili Interface  
South Africa
- MK Macedonia**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia  
  
or  
ELEKTRO - SMK doool  
UL. III Makedonska brigada  
b.b.  
1000 Skopje  
Telephone number +389  
22460295  
Fax number  
[Elektro-smk@telekaibel.net.mk](mailto:Elektro-smk@telekaibel.net.mk)
- MN Mongolia**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- MT Malta**  
E. S. S., Electrical Supplies &  
Services Ltd.  
San Gwakklin Road  
Mriehel  
  
Telephone number +356  
21255777  
Fax number +356 21255999  
[robert.agius@ess.com.mt](mailto:robert.agius@ess.com.mt)
- MU Mauritius**  
Mubelo Electrical Ltd.  
Office 26, Gateway building,  
St Jean Road  
Quatre Bornes  
Mauritius  
Telephone number +230  
4670989  
Fax number +230 4654051  
[richard.mubelo@orange.mu](mailto:richard.mubelo@orange.mu)
- MW Malawi**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.
- MX Mexico**  
W Interconnections S. A.  
DE C. V.  
Blvd. Hermanos Serdán 698,  
Col. San Rafael Oriente  
72029 Puebla  
Telephone number +52 (222)  
268 6227  
Fax number +52 (222) 286  
6242  
[clientes@weidmueller.com.mx](mailto:clientes@weidmueller.com.mx)
- MY Malaysia**  
Connect Plus Technology  
Sdn Bhd  
No. 43, Jalan PJS 11/22,  
Bandar Sunway  
46150 Petaling Jaya  
Selangor Darul Ehsan  
Telephone number +60 3  
5633 7363  
Fax number +60 3 5633  
6562  
[paul@cpctech.com.my](mailto:paul@cpctech.com.my)  
[www.cpctech.com.my](http://www.cpctech.com.my)
- MZ Mozambique**  
Please contact  
Phambili Interface  
South Africa
- NA Namibia**  
Please contact  
Phambili Interface  
South Africa
- NG Nigeria**  
Please contact  
Weidmüller Interface GmbH  
& Co. KG  
South Africa
- NL Netherlands**  
Weidmüller Benelux B. V.  
Franciscusweg 221  
1216 SE Hilversum  
P.O. Box 1505  
1200 BM Hilversum  
Telephone number +31 35  
626 12 61  
Fax number +31 35 623  
20 44  
[info@weidmueller.nl](mailto:info@weidmueller.nl)  
[www.weidmueller.nl](http://www.weidmueller.nl)
- NO Norway**  
Sivilingeniør J.F. Knudtzen AS  
Billingstadsletta 97  
1396 Billingstad  
PO Box 160  
1378 Nesbru  
Telephone number +47 66  
98 33 50  
Fax number +47 66 98 09 55  
[firmapost@jfknudtzen.no](mailto:firmapost@jfknudtzen.no)  
[www.jfknudtzen.no](http://www.jfknudtzen.no)
- NZ New Zealand**  
Cuthbert S. Steward Ltd.  
27 Te Puni Street  
Petone  
PO Box 38496  
Wellington Mail Centre 5054  
Telephone number (04) 568  
6156  
Fax number (09) 489 1752  
[csi@cuthbertsteward.co.nz](mailto:csi@cuthbertsteward.co.nz)  
  
Cuthbert S. Steward Ltd  
4 Fred Thomas Drive  
Aon Building, Ground Floor,  
South Entry  
Takapuna  
PO Box 100 338  
North Shore City 745  
Telephone number (09) 489  
1751  
Fax number (04) 568 6056  
[cslak@cuthbertsteward.co.nz](mailto:cslak@cuthbertsteward.co.nz)
- OM Oman**  
DAN INTERNATIONAL LLC.  
Ghala St. 111  
BP 2901  
Seeb  
Telephone number +968  
5036 77  
Fax number +968 5037 55  
[yedu@danint.com](mailto:yedu@danint.com)
- PE Peru**  
IMPEXINCA S.A.C.  
Calle Ortiz de Zavallos No.  
105, Urb. San Antonio  
18  
Lima, Miraflores  
Telephone number +51 1  
447 5608  
[info@impexinca.pe](mailto:info@impexinca.pe)  
[www.impexinca.pe](http://www.impexinca.pe)  
  
J & W CIA, S. A.  
Calle 6 Mz. D Lte. 23, Urb.  
Ind. Grimanesa  
01  
Callao  
Telephone number +51 1  
572 2539  
Fax number +51 1 572 0152  
[contacto@jwcia.com](mailto:contacto@jwcia.com)  
[www.jwcia.com](http://www.jwcia.com)
- PH Philippines**  
Enclosure Systems Specialists  
Inc.  
2276 Don Chino Roces  
Avenue Extension  
Room 103/105 Narra Building  
1231 Makati City  
Telephone number +63 2  
813 8580  
Fax number +63 2 813 8596  
[sales\\_encsys@pltdsl.net](mailto:sales_encsys@pltdsl.net)  
[www.enclosuresystemsph.com](http://www.enclosuresystemsph.com)
- PK Pakistan**  
Automation Controls (Pak)  
Apartment No. 33 C III,  
Chenab Block, Allama Iqbal  
Town  
Lahore  
Telephone number +92 42  
37809948  
Fax number +92 42  
37809950  
[nadeem@acpak.com.pk](mailto:nadeem@acpak.com.pk)  
[www.acpak.com.pk](http://www.acpak.com.pk)
- PL Poland**  
Weidmüller Sp. z o. o.  
ul. Ogrodowa 58  
00-876 Warszawa  
Telephone number +48 22  
510 09 40  
Fax number +48 22 510  
09 41  
[biuro@weidmueller.com.pl](mailto:biuro@weidmueller.com.pl)  
[www.weidmueller.pl](http://www.weidmueller.pl)
- PR Puerto Rico**  
Please contact  
W Interconnections Inc.  
United States
- PT Portugal**  
Weidmüller Sistemas de  
Interface S. A.  
Estrada Outeiro Polima, R.  
Augusto Dias da Silva, Lote  
B - Esc. 2  
São Domingos de Rana  
2785-515 Abóboda  
Telephone number +351 214  
459 191  
Fax number +351 214  
455 871  
[weidmuller@weidmueller.pt](mailto:weidmuller@weidmueller.pt)  
[www.weidmueller.pt](http://www.weidmueller.pt)  
  
Telephone number +974  
4651441  
Fax number +974 4654579  
[dmtctech@qatar.net.qa](mailto:dmtctech@qatar.net.qa)  
<http://www.dohamotorsgroup.com/td.html>  
  
Petroleum Technology Co.  
W.L.L.  
PO Box 16069  
5th Floor Toyota tower  
Telephone number +974  
44419603  
Fax number +974 44419604  
[petrotec@qatar.net.qa](mailto:petrotec@qatar.net.qa)  
[www.petrotec.com.qa](http://www.petrotec.com.qa)
- PY Paraguay**  
Please contact  
CPI SA  
Argentina
- QA Qatar**  
Doha Motors  
PO Box 145  
  
Telephone number +974  
4651441  
Fax number +974 4654579  
[dmtctech@qatar.net.qa](mailto:dmtctech@qatar.net.qa)  
<http://www.dohamotorsgroup.com/td.html>  
  
Petroleum Technology Co.  
W.L.L.  
PO Box 16069  
5th Floor Toyota tower  
Telephone number +974  
44419603  
Fax number +974 44419604  
[petrotec@qatar.net.qa](mailto:petrotec@qatar.net.qa)  
[www.petrotec.com.qa](http://www.petrotec.com.qa)
- RO Romania**  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Ionescu Crum Street, No.  
1, 1st Tower, 1st Floor,  
Office 4  
500446 Brasov - Brasov  
Business Park  
Telephone number +40 (268)  
446 222  
Fax number +40 (262)  
205 410  
[claudiu.totea@weidmueller.com](mailto:claudiu.totea@weidmueller.com)  
[www.weidmueller.com](http://www.weidmueller.com)
- RS Serbia**  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Ustanička 189, III sprat  
lokal 7a  
11050 Beograd  
Telephone number +381  
112885274  
Fax number +381  
112885274  
[zoran.rabrenovic@weidmueller.com](mailto:zoran.rabrenovic@weidmueller.com)  
  
TeLa Elektrik d.o.o.  
Ul. Dr. Drage Ljočić 6  
Beograd  
Telephone number +381 11  
2772 415  
Fax number +381 11 2772  
850  
[office@tela.rs](mailto:office@tela.rs)  
[www.tela.rs](http://www.tela.rs)
- RU Russia**  
Weidmüller Group  
7/10 Khlebozavodskiy  
Passage,  
Moskau  
115230  
Telephone number +7 495  
280 72 71  
Fax number +7 495 280  
72 71  
[Info@weidmueller.ru](mailto:Info@weidmueller.ru)  
[www.weidmueller.ru](http://www.weidmueller.ru)
- SA Saudi Arabia**  
Al Abdulkarim Holding Co.  
P.O. Box 4  
Dammam 31411  
Telephone number +966 3  
8337110  
Fax number +966 3  
8829547  
E-mail [salehsk@akh.com.sa](mailto:salehsk@akh.com.sa)  
[www.weidmueller.ae](http://www.weidmueller.ae)  
  
Saudi Electric Supply  
Company (SESCO)  
P.O. Box 32 98  
Al Khobar 31952  
Telephone number +966 3  
8829546 Ext. 3030  
Fax number  
E-mail [Safdar.Malik@sescogex.com](mailto:Safdar.Malik@sescogex.com)  
[www.sescogex.com](http://www.sescogex.com)
- SE Sweden**  
Weidmüller AB  
Axel Danielssons väg 271  
BOX 31025  
SE-200 49 Malmö  
Telephone number +46 77-  
143 00 44  
Fax number +46 40-37 48 60  
[info@weidmueller.se](mailto:info@weidmueller.se)  
[www.weidmueller.se](http://www.weidmueller.se)
- SG Singapore**  
Weidmüller Pte. Ltd.  
70 Bendemeer Road  
# 04-03 Luzerne Building  
Singapore 339940  
Telephone number +65 6841  
5311  
Fax number +65 6841 5377  
[info@weidmueller.com.sg](mailto:info@weidmueller.com.sg)  
[www.weidmueller.com.sg](http://www.weidmueller.com.sg)
- SI Slovenia**  
Elektrospoji d. o. o.  
Stegne 27  
SI- 1000 Ljubljana  
Osrednjeslovenska  
Telephone number +386 1  
511 3810  
Fax number +386 1 511  
1604  
[info@elektrospoji.si](mailto:info@elektrospoji.si)  
[www.elektrospoji.si](http://www.elektrospoji.si)
- SK Slovakia**  
ELEKTRIS s.r.o.  
Elektrárnská 1  
831 04 Bratislava  
Telephone number +421  
2/4920 0113  
Fax number +421 2/4920  
0119  
[bratislava@elektris.sk](mailto:bratislava@elektris.sk)

# Addresses worldwide

Let's connect.

**SV El Salvador**  
Prestegard Electro  
11 Avenida Norte No. 240  
Edificio Salazar No. 2  
San Salvador  
Telephone number +503  
2271 1690  
Fax number +503 2221  
3851  
prestegard@navegante.com.sv

**SY Syria**  
Please contact  
Weidmüller Middle East FZE  
United Arab Emirates

**SZ Swaziland**  
Please contact  
Phambili Interface  
South Africa

**TH Thailand**  
Pisanu Engineering Co. Ltd.  
Kwang Dingaeng, Khet  
Dingaeng  
800/2 Soi Trakulsuk, Asoke-  
dindaeng Road  
Dindaeng, Bangkok  
10400  
Telephone number +66 2  
248 2896  
Fax number +662 105 6301  
ecsales@pisanu.co.th  
www.pisanu.co.th  
  
Representative Office  
Weidmüller Pte. Ltd.  
37/F, Sathorn Square Building  
98 North Sathorn Road  
Bangkok, Silom Bangrak  
10500  
Telephone number +66 2  
105 6300  
Fax number +66 2 642 9220  
info@weidmuller.com.sg

**TJ Tajikistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**TM Turkmenistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**TN Tunisia**  
Please contact  
Weidmüller E. U. R. L.  
France

**TR Turkey**  
Weidmüller Elektronik Ticaret  
Ltd. Sirketi  
Kavacik Mah. Orhan Veli Kanik  
Caddesi 9/1  
34810 Beykoz / Istanbul  
Telephone number +90 (216)  
537 10 70  
Fax number +90 (216) 537  
10 77  
info@weidmuller.com.tr  
www.weidmuller.com.tr

**TW Taiwan**  
Weidmüller (Hong Kong)  
Limited  
No. 3, Lane 89, ChungYang  
N. Rd  
24148 SanChuang City,  
Taipei  
Telephone number +886 921  
949 751  
roy.lin@weidmueller.com.hk

**TZ Tanzania**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.

**UA Ukraine**  
LLC WM UKRAINE  
Levanevskogo str. 6  
Kiev  
3058  
Telephone number +38 044  
490 32 48  
Fax number  
info@wm-ua.com.ua  
wm-ua.com.ua/

Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Z, office 303  
7-D, Zdolbunivska str.  
Kiev, 2081  
Telephone number  
(mobile) +38 050 440 25 24  
info.ua@weidmueller.com

**US United States**  
W Interconnections Inc.  
821 Southlake Boulevard  
Richmond Virginia 23236  
Telephone number +1 (804)  
794-2877  
Fax number +1 (804) 379-  
2593  
info@weidmuller.com  
www.weidmuller.com

**UY Uruguay**  
REWUO Uruguay S. A.  
AV. Bolivia 2001Esq  
Rocafuerte  
11300 Carrasco Montevideo  
Telephone number +598  
2604 8439  
Fax number +598 2604  
8439  
rewo@rewouruguay.com.uy

**UZ Republic of Uzbekistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**VE Venezuela**  
Somerinca C. A.  
Corazon de Jesus - 3ra  
Transversal con calle el  
Carmen- Los Dos Caminos  
Caracas 1070-A  
Telephone number +58  
2 122352748  
Fax number +58  
2 122399341  
klocmoeller@cantv.net  
www.somerinca.com

**VN Vietnam**  
ALUMI Industrial Equipment &  
Automation Company Limited  
E1, La Thanh Hotel  
218 Doi Can Street  
Lieu Giai Ward, Ba Dinh  
District  
Hanoi City  
Telephone number +84 4  
37628601  
Fax number +84 4  
62661391  
aumi@aumi.com.vn  
www.aumi.com.vn

Representative Office  
Weidmüller Pte. Ltd.  
Level 16 Saigon Tower  
Building  
29 Le Duan Street  
District 1  
Ho Chi Minh  
Telephone number +848  
3520 7717  
Fax number +848 3520  
7604  
info@weidmuller.com.sg

**ZA South Africa**  
Phambili Interface  
PO Box 193  
1609 Johannesburg, Edenvale  
5 Bundo Road, Sebenza  
1610 Johannesburg  
Telephone number +27 (11)  
4521930  
Fax number  
info@weidmuller.co.za  
www.weidmuller.co.za

Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
210 Amarand  
Avenue, Pegasus Building  
181 Pretoria, waterkloof Glen  
ext 2 -  
Telephone number +27 12  
003 2906  
Fax number +27 (11)  
4526455  
Jacques.Vosloo@weidmueller.  
com  
www.weidmueller.com

**ZM Zambia**  
Please contact  
Phambili Interface  
South Africa

**ZW Zimbabwe**  
Please contact  
Phambili Interface  
South Africa