



## Disconnects T&B Catalog Number:

BD14-183  
78621081447  
Active

## UPC Number: Status: Description:

Non-Insulated Female Disconnect, Length .64 Inches, Width .23 Inches,  
Tab Size .187x.032, Wire Range #16-#14 AWG, Copper, Tin Plated

### WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.

### General

Disconnect Type	Female - 187 Series
Insulation Type	Non-Insulated
Terminal Series	BD
Material	Brass
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	16-14
Tab Size	.187 x .032

### Dimension Information

Stock Thickness	.03
A (inches)	.64
B (inches)	.23

### Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Tool Charts	Available on Website
Application Tools	WT111M, WT112M, ERG4002, WT2000
Recommended Tool	ERG4002

### Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000
Alternate Package Qty	BD183

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

### Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E66716

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)