



**Standard  
T&B Catalog Number:**

TY25M-2

**UPC Number:**

78621084485

**Status:**

Active

**Description:**

Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Military Specified (MIL-SPEC MS3367-1-2), Bulk Pack

**Features**

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

**General**

Material Nylon 6.6  
Color Red

**Dimension Information**

Nominal Length (inches) 7  
Length (inches) 7.31  
Width (inches) .184  
Max. Wire Bundle Diameter (inches) 1.75

**Specifications**

Temperature Rating -40°F to 185°F  
Flammability Rating UL 94 V-2

**Tooling**

Application Tools ERG-299, WT1-TB

**Packaging**

T&B Order Multiple 1000  
T&B Inner Pack 1000  
Package in Units 10000  
Package Type Bulk  
T&B Sold in UOM Each  
T&B Weight Per UOM 5 lbs. per 1000

**Application Support**

Material Selection Guide Available on Website

Available Colors Available on Website

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:

Y

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com