

## Splice Connector T&B Catalog Number:

2RE6

## UPC Number:

78621089466

## Status:

Active

## Description:

Nylon-Insulated Butt Splice, Length 1.85 Inches, Width .45 Inches, Maximum Insulation Diameter .420, Wire Range #6, Color Blue, Copper, Tin Plated

## WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

## Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.

## General

|                 |                     |
|-----------------|---------------------|
| Insulation Type | Insulated Nylon     |
| Terminal Series | RE                  |
| Material        | Copper              |
| Finish          | Electro -Tin Plated |
| Color           | Blue                |
| Wire Range      | 6                   |

## Dimension Information

|                             |      |
|-----------------------------|------|
| Maximum Insulation (inches) | .420 |
| Stock Thickness             | .04  |
| A (inches)                  | 1.85 |
| B (inches)                  | .45  |

## Specifications

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 105°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-2 |

## Tooling

|                   |                      |
|-------------------|----------------------|
| Tool Charts       | Available on Website |
| Application Tools | TBM6, TBM6S, ERG4007 |
| Recommended Tool  | ERG4007, TBM6S       |

## Packaging


|                       |                   |
|-----------------------|-------------------|
| T&B Order Multiple    | 20                |
| T&B Inner Pack        | 20                |
| Package in Units      | 200               |
| Package Type          | Standard          |
| T&B Sold in UOM       | Each              |
| T&B Weight Per UOM    | 1.81 lbs. per 100 |
| Alternate Package Qty | REE28             |

## Application Support

|                   |                      |
|-------------------|----------------------|
| Overview          | Available on Website |
| Wire Guide Tables | Available on Website |

## Certifications

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|



## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)