



**Ferrule**  
**T&B Catalog Number:**

F2024  
 78621033990  
 Active

**UPC Number:**  
**Status:**  
**Description:**


Polypropylene-Insulated Ferrule, Total Length .551 Inches/14.0mm, Pin Length .315 Inches/8mm, Pin Diameter .051 Inches/1.3mm, Base Diameter .11 Inches/2.8mm, Wire Range 18 AWG/.75mm<sup>2</sup>, Color Gray, Copper, Tin Plated

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



**General**

Ferrule Type	Insulated
Insulation Type	Polypropylene
Material	Copper
Finish	Electro -Tin Plated
Color	Gray
Wire Range	18
Wire Size (mm <sup>2</sup> )	.75

**Dimension Information**

A (mm)	14.0
B (mm)	8.0
Diameter C (inches)	.051
Diameter C (mm)	1.3
Diameter D (inches)	.110
Diameter D (mm)	2.8
E (mm)	.15
A (inches)	.551
B (inches)	.315
E (inches)	.006

**Specifications**

Temperature Rating	105°C
Flammability Rating	94HB

**Tooling**

Tool Charts	Available on Website
Application Tools	T1, T3, ERG4
Recommended Tool	T1, T3, ERG4

**Packaging**

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

**Application Support**

Overview	Available on Website
Wire Guide Tables	Available on Website

## Notes

Ferrule dimensions conform to DIN 46228, Part 4.

## Certifications

RoHS Compliance	Yes
-----------------	-----

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com