



Loop Ties

T&B Catalog Number:

FO200-50-0

UPC Number:

78621071240

Status:

Active

Description:

FO Slotted Loop Tie, Black Polyamide (Nylon 6.6) on Hook Side and Low Density Polyethylene on Loop Side for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 228.6mm (9.0 Inches), Width of 19.05mm (0.75 Inches), Thickness of 1.588mm (0.0625 Inches), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

Features

Enables quick and convenient bundling of data and fiber optic cables.

Screw and adhesive mounting bases provide multiple mounting options.

Wrap pre-determined bundle diameters using the convenient slotted head.

General

Material Nylon

Color Black

Dimension Information

Nominal Length (inches) 9

Length (inches) 9

Width (inches) .750

Max. Wire Bundle Diameter (inches) 2

Specifications

Temperature Rating -40°F to 220°F

Packaging

T&B Order Multiple 10

T&B Inner Pack 10

Package in Units 100

Package Type Regular

T&B Sold in UOM Each

T&B Weight Per UOM 1 lbs. per 100

Application Support

T&B Sales Drawings wsd-000067

Overview Available on Website

Material Selection Guide Available on Website

Notes

Black is standard color. Multiple colors available for identifying specific bundles. Add -FR for UL94V-2 rated material after color choice.

Certifications

RoHS Compliance Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

