



## Rolled Hook and Loop T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

FOR180-50-0  
78621073605  
Active

FOR Roll Hook and Loop Tie, Black Polyethylene/Nylon for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 4572.0mm (180 Inches), Width of 19.05mm (0.75 Inches), Thickness of 1.588mm (0.0625 Inches), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

### Features

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Rolled hook and loop material enables custom cut lengths, avoiding waste.

### General

Material	Nylon
Color	Black

### Dimension Information

Nominal Length (inches)	180
Length (inches)	180
Width (inches)	.750
Max. Wire Bundle Diameter (inches)	5

### Specifications

Temperature Rating	-40°F to 220°F
--------------------	----------------

### Packaging

T&B Inner Pack	1
Package in Units	10
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	14.19 lbs. per 100

### Application Support

T&B Sales Drawings	wsd-000067
Overview	Available on Website
Material Selection Guide	Available on Website

### Notes

Black is standard color. Multiple colors available for identifying specific bundles. Add -FR for UL94V-2 rated material after color choice.

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com