

Type B Liquidtight Tubing & Fittings

T&B Catalog Number:

EFC038

UPC Number:

78621078960

Status:

Active

Description:

3/8 Inch Black Corrugated PVC Flexible Tubing



Features

Maximum flexibility in tight applications.

Extremely fast installation

Liquidtight with specified fittings.

Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

Application

Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship-board wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

General

Material

PVC

Color

Black

Working Temperatures

-18 C to +60 C

Dimension Information

Size (inches)

3/8

I.D. - Minimum (inches)

0.484

I.D. - Maximum (inches)

0.504

O.D. - Minimum (inches)

0.69

O.D. - Maximum (inches)

0.71

Packaging

T&B Order Multiple

100

Package in Units

100

T&B Sold in UOM

Feet

T&B Weight Per UOM

10.25 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications

Available on Website

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 96548

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com