



**Fork Terminal**  
**T&B Catalog Number:**

14RB-14F

**UPC Number:**

78621083820

**Status:**

Active

**Description:**

Vinyl-Insulated Fork Terminal, Length 1.11 Inches, Width .44 Inches, Maximum Insulation .170, Bolt Hole 1/4 Inch, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated


**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded.



**General**

|                 |                     |
|-----------------|---------------------|
| Insulation Type | Insulated Vinyl     |
| Terminal Series | RB                  |
| Material        | Copper              |
| Finish          | Electro -Tin Plated |
| Color           | Blue                |
| Wire Range      | 18-14               |
| Stud Size       | 1/4                 |

**Dimension Information**

|                             |      |
|-----------------------------|------|
| Maximum Insulation (inches) | .170 |
| Stock Thickness             | .03  |
| A (inches)                  | 1.11 |
| B (inches)                  | .44  |
| C (inches)                  | .38  |
| M (inches)                  | .89  |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 105°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

|                   |  |
|-------------------|--|
| Tool Charts       | Available on Website                     |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003 |
| Recommended Tool  | ERG4001                                  |

**Packaging**

|                       |                   |
|-----------------------|-------------------|
| T&B Order Multiple    | 100               |
| T&B Inner Pack        | 100               |
| Package in Units      | 500               |
| Package Type          | Standard          |
| T&B Sold in UOM       | Each              |
| T&B Weight Per UOM    | 0.37 lbs. per 100 |
| Alternate Package Qty | RB1717            |

**Application Support**

|          |                      |
|----------|----------------------|
| Overview | Available on Website |
|----------|----------------------|

Wire Guide Tables

Available on Website

## Certifications

RoHS Compliance

Yes

## Certifications



File Nbr:

E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com