



**Two-Directional
T&B Catalog Number:**

TC5828

UPC Number:

78621087359

Status:


Active

Description:

Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 22.48mm (0.885 Inches), Width of 10.16mm (0.40 Inches), Height of 3.8mm (0.15 Inches), Screw Mounting Method, #8 Hex Head Screw, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

Features

These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.



General

T&B Replacement Catalog Number	TC828-TB
Material	Nylon 6.6
Color	Natural
Mounting Method	Screw
Stud Size	#8 Screw
Max Tie Width Accepted	.19
For Cable Ties	Up to 50 lbs.

Dimension Information

Length (inches)	.875
Width (inches)	.390

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com