

## Splice Connector T&B Catalog Number:

RBB21

## UPC Number:

78621081951

## Status:

Active

## Description:

Nylon Insulated Butt Splice, Length 1.19 Inches, Width .21 Inches, Maximum Insulation Diameter .148, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

## WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

## Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.

## General

Insulation Type	Insulated Nylon
Terminal Series	RBB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

## Dimension Information

Maximum Insulation (inches)	.148
Stock Thickness	.03
A (inches)	1.19
B (inches)	.21

## Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

## Tooling

Tool Charts	Available on Website
Application Tools	ERG4001, ERG4003, WT145C, WT112M
Recommended Tool	ERG4001

## Packaging


T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	3.75 lbs. per 1000
Alternate Package Qty	2RB14

## Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

## Certifications

RoHS Compliance	Yes
-----------------	-----



## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)