



**Type B Liquidtight Conduit Tubing & Fittings**  
**T&B Catalog Number:**

**UPC Number:** LT950P  
**Status:** 78621045072  
**Description:** Active

1/2 Inch 90 Degree Non-metallic Liquidtight Bullet

**Features**

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

**Application**

T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

**General**

Trade Size (inches) 1/2  
 Material Thermoplastic

**Dimension Information**

Dimension A (inches) 0.570  
 Dimension B (inches) 1.489  
 Dimension C (inches) 1.448  
 Dimension D-Minimum Throat (inches) 0.55  
 Dimension F (inches) 1.986  
 A (mm) 14.48  
 B (mm) 37.82  
 C (mm) 36.78  
 D (mm) 13.97  
 F Approx. (mm) 50.44

**Specifications**

3dmodel Available on Website

**Packaging**

T&B Inner Pack 10  
 Package in Units 50  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 7.5 lbs. per 100

**Application Support**

T&B Instruction Sheets ta00970-tb2  
 Guide to Nonmetallic Conduit Applications Available on Website  
 XTRAFLEX System Specifications Available on Website

**Certifications**

RoHS Compliance Yes

## Certifications



File Nbr:  
E 23018

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)