



Type B Liquidtight Conduit Tubing & Fittings
T&B Catalog Number:

UPC Number: LT975P
 78621045073
Status: Active
Description:

3/4 Inch 90 Degree Bullet Connector

Features

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

Application

T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
 Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

General

Trade Size (inches) 3/4
 Material Thermoplastic

Dimension Information

Dimension A (inches) 0.582
 Dimension B (inches) 1.790
 Dimension C (inches) 1.740
 Dimension D-Minimum Throat (inches) 0.74
 Dimension F (inches) 2.212
 A (mm) 14.78
 B (mm) 45.47
 C (mm) 44.20
 D (mm) 18.8
 F Approx. (mm) 56

Specifications

3dmodel Available on Website

Packaging

T&B Inner Pack 10
 Package in Units 50
 T&B Sold in UOM Each
 T&B Weight Per UOM 17 lbs. per 100

Application Support

T&B Instruction Sheets ta00970-tb2
 Guide to Nonmetallic Conduit Applications Available on Website
 XTRAFLEX System Specifications Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com