

Type B Liquidtight Tubing & Fittings

T&B Catalog Number:

LTC150-TB

UPC Number:

78621078958

Status:

Active

Description:

1 1/2 Inch Black Non-metallic Type B Industrial Grade Liquidtight Conduit



Features

Fast installation, even in tight or cramped spaces.

Smooth inner diameter allows easy wire pulling.

Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.

Lightweight and liquidtight.

Application

Machine tools, motor hookups, food processing equipment, extensions from wire ways, and sensor and micro switch wiring found in control consoles.

General

Material	PVC
Color	Black
Working Temperatures	-18 C to +105 C

Dimension Information

Size (inches)	1 1/2
I.D. - Minimum (inches)	1.575
I.D. - Maximum (inches)	1.6
O.D. - Minimum (inches)	1.865
O.D. - Maximum (inches)	1.9

Packaging

T&B Order Multiple	50
Package in Units	50
T&B Sold in UOM	Feet
T&B Weight Per UOM	52.25 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications	Available on Website
XTRAFLEX System Specifications	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com