



Ring Terminal
T&B Catalog Number:

NW10-10

UPC Number:

78621076984

Status:

Active

Description:

Non-Insulated High-Temperature Ring Terminal, Length .66 Inches, Width .31 Inches, Bolt Hole #10, Wire Range #12-#10 AWG, 1200 Degree Fahrenheit Maximum, Nickel Alloy, Plain Finish


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

For easily installed, permanent terminations of solid, round, or stranded nichrome wires as used in toasters, heaters, etc.



General

Insulation Type	Non-Insulated - High Temperature
Terminal Series	NW
Material	Nickel Alloy
Finish	Plain
Color	Metallic
Wire Range	12-10
Stud Size	#10

Dimension Information

Stock Thickness	.40
A (inches)	.66
B (inches)	.31
C (inches)	.28
M (inches)	.51

Specifications

Temperature Rating	1200°F
Voltage Rating	600V

Tooling

Tool Charts	Available on Website
Application Tools	WT1377
Recommended Tool	WT1377

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. per 1000

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com