



Einhell

GC-RS 2540 CB

CLASSIC

GC-RS 2540 CB
Electric Silent Shredder
Art.-Nr.: 3430598
Ident-Nr.: 11014

The GC-RS 2540 CB electric silent shredder is a robust and extremely powerful tool for the quiet shredding of thick materials such as branches as well as tree cuttings, hedge cuttings and garden waste at a high rate of throughput. Its long-lasting cutter drum powerfully draws the material into the large funnel opening. For easy and user-friendly transportation there is a robust chassis with wheels and a practical transport handle.

Features

- Cutter drum
- Generous funnel opening
- Reverse running switch
- Robust chassis with wheels
- Transparent debris box for easy collection and transportation
- Integrated safety switch on the debris box for shredded material
- Integrated plug for power cable
- Practical transport handle

Technical Data

- | | |
|-------------------------|----------------------|
| • Mains supply | 230-240 V 50 Hz |
| • Power | 2000 W |
| • Max. power (S6 S6%) | 2500 W 40 % |
| • Idle speed | 40 min ⁻¹ |
| • Max. branch diameter | 40 mm |
| • Capacity of catch box | 60 L |
| • Sound power level LWA | 94 dB (A) |



Logistic Data

- | | |
|--------------------------------------|--------------------|
| • Product weight | 28 kg |
| • Gross weight single packaging | 30 kg |
| • Dimensions single packaging | 570 x 415 x 515 mm |
| • Pieces per export carton | 1 Pieces |
| • Gross weight export carton | 32 kg |
| • Dimensions export carton | 570 x 415 x 515 mm |
| • Container quantity (20"/40"/40"HC) | 210 448 560 |

Illustrations can contain accessories, which are not included in standard extent of delivery
Illustration similar (in design), production-wise modifications reserved
GS mark belongs to the product itself only, excluded accessory