



Einhell

GH-EH 4245 Electric Hedge Trimmer

Art.-No. 34.034.60

Features

- ON/OFF-dead man's safety switch (1)
- Additional handle for optimal handling (2)
- Large hand protection shield (3)
- Aluminium knife cover (4)
- Counter rotating, double safety blades made of laser-cut and diamond cut steel (5)
- Protection sleeve (not illustrated)
- Cable strain relief (6)
- Metal gearing for long life
- Bumper-guard with bore hole for wall hanging
- Softgrip
- Low weight for comfortable handling

Technical Data

- Mains: 230 V ~ 50 Hz
- Power: 420 W
- Cutting length: 450 mm
- Cutting thickness: 12 mm
- Sword length: 510 mm
- Teeth spacing: 16 mm
- Cuts per minute: 3,200
- Product weight: 2.5 kg

Logistic Data

- Net weight: 2.6 kg
- Gross weight: 3.3 kg
- Packing dimensions: 920 x 175 x 175 mm
- Bar code: 4006825 585049
- Sales unit: 4 pcs

