



Einhell

CLASSIC

GC-EH 5550

Electric Hedge Trimmer

Item No.: 3403360

Ident No.: 11015

Bar Code: 4006825610703

The GC-EH 5550 electric hedge trimmer is a high-quality, powerful and reliable tool which meets the highest requirements for trimming hedges, shrubs and bushes. For optimum power transmission there is a robust metal gearing. The counter-rotating double-bladed safety cutters are made of laser-cut and diamond-ground steel and achieve outstanding cutting results. For safe operation the handle has an anti-slip soft grip, and an additional handle makes this low weight hedge trimmer very comfortable to use. The GC-EH 5550 is equipped with a dead man's safety switch, and for additional safety there is also a large hand shield.

Features

- Low weight for comfortable handling
- Softgrip
- ON/OFF-dead man's safety switch
- Additional handle for optimal handling
- Large hand protection shield
- Aluminium knife cover
- Safety blades made of laser-cut and diamond cutted steel
- Metal gearing for long life
- Cutting collector
- Cable strain-relief clip



Technical Data

- Mains supply	230 V 50 Hz
- Power	550 W
- Idle speed	1500 min ⁻¹
- Sword length	560 mm
- Cutting length	500 mm
- Spacing between teeth	26 mm
- Cuts per minute	3000 min ⁻¹

Logistic Data

- Product weight	3.3 kg
- Gross weight single packaging	4.32 kg
- Dimensions single packaging	930 x 175 x 205 mm
- Pieces per export carton	4 Pieces
- Gross weight export carton	19 kg
- Dimensions export carton	955 x 370 x 270 mm
- Container quantity (20"/40"/40"HC)	1200 2432 2816

