



GC-SA 1231

Electric Scarifier-Lawn Aerat.

DRAFT

Item No.: 3420620

Ident No.: 11026

Bar Code: 4006825603804

The electric scarifier/aerator GC-SA 1231 is a powerful and reliable combined device doing a good job in aerating and scarifying small to middle size plots for a healthy lawn care. With 8 high-quality double blades, the ball bearing mounted cutting roller removes weeds and moss with their roots thoroughly. The also ball bearing mounted aerator roller allows a professional soil aeration with 42 claws. For that purpose, the powerful inverse-speed motor with 1,200 Watt delivers a strong torque for continuous working progress and consistently good results. The robust plastic housing is a guarantor for durability, and the 28 liters collector bag is included. The device is recommended for lawns up to ca. 300 m².

Features

- Powerful series-wound motor
- Combination tool: scarifier and aerator
- Ball-bearing spike drum with 8 double blades
- Ball-bearing aerator roller with 42 claws
- Adjustable scarifying depth, 3 levels, with parking position
- Folding long handle
- Wide wheels exert less stress on the lawn
- Large catch bag 28 l
- Impact-resistant plastic housing
- Recommended for lawn areas up to 300 m²

Technical Data

- Mains supply	230 V 50 Hz
- Power	1200 W
- Working width	310 mm
- Number of knives	8 Pieces
- Number of claws	42 Pieces
- Wheel diameter front	170 mm
- Wheel diameter rear	60 mm
- Capacity of catch bag	28 L
- Working depth	3 settings 9 mm

Logistic Data

- Product weight	0 kg
- Gross weight single packaging	0 kg