



Einhell

EXPERT Plus

TE-HD 18 Li Kit

Cordless Rotary Hammer

Item No.: 4513810

Ident No.: 11014

Bar Code: 4006825604047

The cordless drill hammer TE-HD 18 Li Kit is a robust and versatile power house for screwing and drilling jobs with additional powerful hammer function and independence from mains. Thanks to its pneumatic hammer mechanism a highly good propulsion in concrete is enabled. Due to its ergonomic handle with soft grip the drill can be handled comfortably and safely at every time. Quick stop, LED light and the automatic SDS-Plus chuck enable comfortable operations . The 30 minutes high-speed battery charger enables quick charging of the powerful 18 Volt system battery which can be used in several further Power X-Change family devices. A carrying case is included in delivery.

Features

- Member of the Power X-Change family
- Li-Ion battery: no self-discharging/small/light/easy to handle
- 3 functions: screwdriving, drilling, hammer drilling in concrete
- Pneumatic hammer action for easy drilling in concrete
- Powerful motor and metal gearing for high torque
- Universal SDS-plus-bit mounting with auto-slip-in function
- Finely adjustable speed electronics for sensitive jobs
- Charge state can be viewed on the battery capacity indicator
- Ergonomic grip area with softgrip
- Incl. LED-light to illuminate working area
- Incl. 30-min high-speed charger and Power X-Change battery
- Delivery in handy case



Technical Data

- Accumulator	18 V 1500 mAh Li-Ion
- Charging time	1/2h
- Idle speed (gear 1)	0-1100 min ⁻¹
- Impact rate (gear 1)	0-5700 min ⁻¹
- Impact power	1.2 J
- Max. torque hard	9.9 Nm
- Drilling capacity in concrete	12 mm

Logistic Data

- Tool weight	1.76 kg
- Gross Weight	4.1 kg
- Dimensions single packaging	415 x 112 x 325 mm
- Pieces per export carton	4 Pieces
- Gross weight export carton	20 kg
- Dimensions export carton	492 x 460 x 295 mm
- Container quantity (20"/40"/40"HC)	1616 3296 3892

